

PHILIPS

Pedestal/Pathway
Lights 0.05W

Outdoor Solar

3000K

Black

Water Resistant

046677608767



Solar-powered garden light for all seasons

Long-lasting solar light that saves you money

Ease of use

- A full range of available applications

Decorate your garden with light

- Opt for pedestal lights

Highlights

A full range of available applications

Ideal outdoor lighting for a garden, terrace, pathway or balcony, Philips outdooras wall, post, pedestal and ceiling lights create a cosy, relaxing atmosphere when the sun goes down, as well as providing the reassurance of being able to see safely after dark.

Opt for pedestal lights



Enhance your outdoor space with this pedestal lamp, the perfect lighting for your garden, the edge of your terrace or as illumination of a driveway and paths.

Specifications

Bulb characteristics

- Dimmable: No

Design and finishing

- Color: Black
- Material: Plastic

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Anti rust anti dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: No
- Fully weatherproof: Yes
- LED integrated: No
- Motion sensor: No
- Solar Energy: Yes

Light characteristics

- Color rendering index (CRI): ≥80

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Pedestal/Pathway Lights
- EyeComfort: No
- LED Innovations: EyeComfort
- Extra Features: Water Resistant

Product dimensions and weight

- Net weight: 1.782 kg
- Overall height: 2-1/8 inch

Service

- Warranty: 1 year(s)

Technical specifications

- Total lumen output fixture: 8
- Bulb technology: LED
- Light color: 3000
- Mains power: DC 1.3
- Wattage bulb included: 0.05
- Class of protection: Class III - Safe Extra Low Voltage
- Light source replaceable: No
- UL Wet/ damp/ dry location: Wet location

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 046677608767
- Net weight: 1.78 kg
- Gross weight: 2.38 kg
- Height: 24.8 cm
- Length: 32.7 cm
- Width: 18.5 cm



Issue date: 2026-05-14
Version: 0.70

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com