

# PHILIPS

## Desk Light

Desk Lights

3000/6500/4500K

Green

Tunable White

046677609245



## Superior light and style

Make any room glow in your favorite color

### **Durability**

- Long life span up to 15,000 hours

### **Create the perfect atmosphere**

- Enjoy high-quality light that's easy on your eyes and easily adjust the brightness to suit each moment; with a minimalist slim design, the Philips Cilantro spotlight works with almost any decor.

# Highlights

## Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

## Create the perfect atmosphere

Enjoy high-quality light that's easy on your eyes and easily adjust the brightness to suit each moment; with a

minimalist slim design, the Philips Cilantro spotlight works with almost any decor.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Dimmable: Yes

## Design and finishing

- Color: Green
- Material: Metal

## Durability

- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: No
- Remote control included: No

## Light characteristics

- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

## Miscellaneous

- Especially designed for: Living Room
- Style: Modern
- Type: Desk Lights
- EyeComfort: No
- Extra Features: Tunable White

## Product dimensions and weight

- Net weight: 1.18 kg
- Overall height: 1-5/16 inch

## Service

- Warranty: 1 year(s)

## Technical specifications

- Total lumen output fixture: 100
- Bulb technology: LED
- Light color: Tunable white (warm white, natural white and cool white on switch toggle)
- Mains power: DC 4.2
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class III - Safe Extra Low Voltage

## The bulb

- Software upgradable: No

## What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

## Packaging dimensions and weight

- EAN/UPC - product: 046677609245
- Net weight: 1.18 kg
- Gross weight: 1.35 kg
- Height: 16.5 cm
- Length: 13 cm
- Width: 13 cm



Issue date: 2026-05-14  
Version: 0.80

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)