

PHILIPS

Kinno Wall Lights
7.2W E26

Outdoor luminaires

2700K

Black

Dusk to Dawn; Water Resistant



046677609474



Enjoy a beautiful garden with light

The Philips wall light illuminates and lightens up your entrance with diffused and warm white light, with dusk-to-dawn LED bulb included, the light can automatically turn on at night and off in the morning.

Bring design into your garden

- Stylish contemporary designs for your garden

Premium quality

- High quality aluminum and real glass

Designed for outdoors

- IP44 - weather proof

Special characteristics

- Unique day/night function

High quality light

- Warm white light 2700K

Highlights

Stylish contemporary designs for your garden

The contemporary designs by Philips are stylish but understated, beautiful by day or night without overwhelming your garden or terrace. There are a full range of lights to choose from, so there is bound to be one to match your outside space and taste.

High quality aluminum and real glass



This Philips light is made specifically for outdoor spaces. It's hard-wearing and built to last, so it will light up your garden night after night. It's constructed from high quality die-cast aluminum and real glass.

IP44 - weather proof




This Philips outdoor light is especially designed for humid outdoor environments and has been tested rigorously to ensure water resistance. Its IP44 rating means that it has been certified to offer ingress protection against dust and splashing water—perfect for general outdoor use.

Unique day/night function



Thanks to the day/night function, this outdoor light automatically switches on when it gets dark outside. Use this unique function for long evenings or for safety reasons.

Warm white light 2700K



Did you know that different shades of white light are identified by different color temperatures, measured in Kelvin (K)? Lower color temperatures produce a warm, cozy white light, while higher color temperatures produce a cool, more energizing white light. This luminaire produces warm, relaxing light at 2700 K.

Specifications

Bulb characteristics

- Dimmable: No

Design and finishing

- Color: Black
- Material: Glass, Metal

Durability

- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: No
- Anti rust anti dust: Yes
- Bi-directional light beams: No
- Day-and-night sensor: Yes
- Fully weatherproof: Yes
- LED integrated: No
- Motion sensor: No
- Solar Energy: No
- Centerpiece: No

Light characteristics

- Color rendering index (CRI): 90
- Color temperature: 2700 K

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No
- Extra Features: Dusk to Dawn, Water Resistant

Product dimensions and weight

- Net weight: 1.89 kg
- Overall height: 10 inch

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: 800
- Bulb technology: LED
- Light color: Warm white light
- Mains power: AC 120
- Fitting/cap: E26
- Wattage bulb included: 7.2
- IP code: IP44
- Class of protection: Class I - Earthed
- Light source replaceable: Yes
- Number of light sources: 1
- UL Wet/ damp/ dry location: Wet location

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 046677609474
- Net weight: 1.89 kg
- Gross weight: 2.36 kg
- Height: 32 cm
- Length: 26.7 cm
- Width: 21.7 cm



Issue date: 2026-06-06
Version: 0.88

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com