

PHILIPS

Smart Home Remote
Control, Customizable
Buttons, 50 ft Range

Smart Accessory

Customizable buttons

Wide range 15 m

Works without Wi-Fi



046677609863



Fingertip light control

Enjoy simple, reliable control over your smart lighting with an intuitive nine-button remote that lets you switch lights on or off, dim brightness, select from four preset modes, or activate a night light in seconds. The four numbered buttons can be customized in the WiZ app to create shortcuts to your favorite scenes, while a reliable 15-metre range ensures smooth control throughout your home. Because it connects directly to your lights without relying on Wi-Fi, it works dependably at all times. Easy to set up using the WiZ app and fully compatible with all Connected by WiZ products.

Easy setup

- Setup couldn't be easier

Smart control

- Wide range
- Customizable buttons
- Convenient controls
- Connected by WiZ

Highlights

Setup couldn't be easier

Download the WiZ app, connect your device to the power, and then connect it to your Wi-Fi network. And now you can start using it!

Wide range

Control lights and devices within a range of 15 meters or 50 feet in any normal indoor environment with partitions and walls.

Customizable buttons

Use the WiZ app to customize the light mode buttons on your remote, creating easily accessible shortcuts to your favorites.

Convenient controls

Switch your lights on or off, adjust the brightness, select different light modes, and use the night light— even when the Wi-Fi is down.

Connected by WiZ

Fully compatible with all Connected by WiZ products—use the WiZ app to set up and unlock all the benefits of smart lighting.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: Black
- Material: Plastic

Extra feature/accessory incl.

- Batteries included: Yes
- Control Distance: 15 m

Power consumption

- Voltage: 3 V

Product dimensions and weight

- Net weight: 0.057 kg
- Overall height: 1/16 inch
- Overall length: 9/16 inch
- Overall width: 3/16 inch

Service

- Warranty: 2 year(s)

Technical specifications

- Battery type: AAA (LR03)
- IP code: IP20
- Class of protection: Class III - Safe Extra Low Voltage

What's supported

- Defined support period: Minimum of 60 months after introduction date
- Max. number of accessories: 9999
- Compatible operating systems: iOS, Android

Packaging dimensions and weight

- EAN/UPC - product: 046677609863
- Net weight: 0.06 kg
- Gross weight: 0.08 kg
- Height: 13.2 cm
- Length: 4.6 cm
- Width: 7.6 cm



Issue date: 2026-05-26
Version: 0.91

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com