PHILIPS

Limbali Ceiling/Wall Spotlight 3x

Ceiling/Wall Spotlights

No bulb

Black

ClickFix



8719514465251



The accent on style

Include this practical Philips spotlight in your home. Choose your Philips GU10 LED bulb to go with your spot style and ensure a high quality and long lasting light.

Special characteristics
- Adjustable spot head

Superior design for an optimal light effect
- Long lasting, high quality material

Highlights

Adjustable spot head



Direct the light where you want it most by simply adjusting, rotating or tilting the spot head of the lamp.

High quality material

This spot light is made of long lasting, high quality materials with superior finishing. This ensures a solid and durable product which will enhance and light up your home for many years to come.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: Black
- Material: Metal

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Adjustable spot head: Not adjustable
- click!FIX mounting: Yes

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Office, Hall
- Style: Contemporary
- Type: Ceiling/Wall Spotlights
- EyeComfort: No
- Extra Features: ClickFix

Product dimensions and weight

- Net weight: 0.56 kg
- Overall height: 130 mm
- Overall length: 293 mm
- Overall width: 293 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: -
- Mains power: AC 220-240
- Fitting/cap: GU10
- Wattage bulb included: 50W
- Maximum wattage replacement bulb: 50
- IP code: IP20 | Finger-protected
- Class of protection: Class I - Earthed
- Number of light sources: 3

Packaging dimensions and weight

- EAN/UPC - product: 8719514465251
- Net weight: 0.56 kg
- Gross weight: 0.7 kg
- Height: 28 cm
- Length: 9.5 cm
- Width: 30 cm

8719514465251

Issue date: 2025-08-30
Version: 0.305

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com