



#### Accessories (Order Separately)

- ORB BK** – Outdoor 4" Round Surface Mount Junction Box, Black
- ORB BZ** – Outdoor 4" Round Surface Mount Junction Box, Bronze
- OSB BK** – Outdoor Single Gang, Surface/Recessed 2-3/4" x 4-1/2" Junction Box, Black
- OSB BZ** – Outdoor Single Gang, Surface/Recessed 2-3/4" x 4-1/2" Junction Box, Bronze

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

#### Example: CEF1RBZ20WF

<b>CEF</b>				
<u>Series</u>	<u># of Heads</u>	<u>Type of Mounting Plate</u>	<u>Color</u>	<u>Lamp Type</u>
CEF – Decorative Outdoor Remote Head	1 – Single Remote Head 2 – Double Remote Head	R – 4" Round Mounting Plate S – Single Gang Rectangular Mounting Plate	BK – Black BZ – Bronze	Blank – No Lamps Installed  MR16 LED Lamp 7F – 12 V, 7 W Flood 35°

#### codes and standards

- UL 924 listed

#### construction

- Constructed of durable die cast aluminum .
- Available in black or bronze .

#### installation

- CEF Series has single or double mounting plates available .

#### lamps

- CEF Series is available with a 12 V , 7 W MR16 LED lamp option .
- CEF Series , lamps included unless specified otherwise .




# CEF Outdoor remote lamp heads


## 12V MR16

### dimensions


single CEF with round mounting plate




double CEF with round mounting plate



single CEF with rectangular mounting plate




double CEF with rectangular mounting plate




junction boxes for CEF

ORBBZ



OSBBZ



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 800-555-0050

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.