



COLOR FILTERS

Description	2"	2 1/2"	3 3/4"	4 11/16"	6 5/16"
Red Gel	L112	F22-20			
Ultraviolet	L114		L414	L214	L314
Red Dichroic	L120	F76-20			
Amber Dichroic	L121	F72-20			
Yellow Dichroic	L122	F75-20			
Green Dichroic	L123	F73-20			
Daylight Blue Dichroic	L124				
Blue Dichroic	L125				
Peach Dichroic		F71-20			
Medium Blue Dichroic		F74-20			
Dark Blue Dichroic		F77-20			
Light Blue Dichroic		F78-20			
Neutral Density		F79-20			
Magenta		F80-20			
Cosmetic 2700° Dichroic	L127				
Yellow Gel	L130	F55-20			
Amber Gel	L131				
Medium Pink			L411	L211	
Warm Red			L412	L212	L312
Daylight Blue			L420	L220	L320
Medium Blue		F33-20	L421	L221	
Medium Amber			L431	L231	L331
Medium Green		F44-20	L441	L241	L341
Straw					L330
Mercury		F66-20			



BEAM MODIFYING LENSES

Description	2"	2 1/2"	4 11/16"
Diffuse Sand Blasted Lens	L110		
Soft Focus Lens	L111		
Prismatic Spread Lens for MR16	L113		
Linear Spread Lens for MR16	L115		
Linear Spread Lens for PAR			L250
Prismatic Spread Lens for PAR			L265
PAR20 Linear Spread Lens		LSL-20	
Overall Spread Lens		OSL-20	
Diffused Lens		DIF-20	



L252, L352 MEDIA HOLDERS


SOURCE	Finish	L252	L352	Description
Medium Pink Filter	Black [MB]	L411	L211	Allows use of L400 series color filters and Cube cell louvers with L1830 (L252) and L1838 (L352).
Warm Red Filter	Black [MB]	L412	L212	
Daylight Blue Filter	Black [MB]	L420	L220	
Medium Blue Filter	Black [MB]	L421	L221	
Medium Amber Filter	Black [MB]	L431	L231	
Medium Green Filter	Black [MB]	L441	L241	
UV Filter	Black [MB]	L414	L214	
Cube Cell	Black [MB]	L274	L275	

L252

Description
MEDIA HOLDER ACCESSORY, BLACK For use with LZR1330 - Allows use of L274 Cube Cell louver and L400 Series Color Filters Finishes: Black (MB)

L352

Description
MEDIA HOLDER ACCESSORY, BLACK For use with LZR1338 - Allows use of L275 Cube Cell louver and L200 Series Color Filters. Finishes: Black (MB)



Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative or visit www.cooperlighting.com for available options, accessories and ordering information.