




Functional and Affordable

GreenUp Linear

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Linear is the entry level linear product family, which offers the basic functional lighting performance, with multiple choices of installations, lumen outputs and product dimensions.

Benefits

- Slim body while delivering powerful lumen outputs.
- Complete family offering, meet basic functional lighting requirements.
- Energy efficiency
- Ensured quality and reliability.





Features

- Wide range of product dimensions and installation options.
- Multiple options of lumen outputs and optics.
- System efficacy up to 95lm/W.

Application

- Retail
- Hospitality
- Fashion

Dimensional drawing



General Information	
CE mark	-
Light Technical	
Optical cover type	Polycarbonate Diffuser
Color rendering index (CRI)	>80
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Temperature	
Ambient temperature range	+20 to +40 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	White RAL 9003
Approval and Application	
Protection class IEC	Safety class II
Mech. impact protection code	IK03
Ingress protection code	IP20
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
53154399	SM308C P22/830 L75W3 PSU MB WH	3000 K	95 lm/W	2,090 lm
53028799	SM308C P22/830 L75W3 PSU WB WH	3000 K	95 lm/W	2,090 lm
52524599	SM308C P22/840 L75W3 PSU MB WH	4000 K	98 lm/W	2,150 lm
52440899	SM308C P22/840 L75W3 PSU WB WH	4000 K	98 lm/W	2,150 lm
52605199	SM308C P22/865 L75W3 PSU MB WH	6500 K	98 lm/W	2,150 lm
52869799	SM308C P22/865 L75W3 PSU WB WH	6500 K	98 lm/W	2,150 lm
52350099	SM308C P30/830 L120W3 PSU MB WH	3000 K	95 lm/W	2,850 lm
52767699	SM308C P30/830 L120W3 PSU WB WH	3000 K	95 lm/W	2,850 lm
53156799	SM308C P30/840 L120W3 PSU MB WH	4000 K	98 lm/W	2,950 lm
53030099	SM308C P30/840 L120W3 PSU WB WH	4000 K	98 lm/W	2,950 lm
52870399	SM308C P30/865 L120W3 PSU MB WH	6500 K	98 lm/W	2,950 lm
52351799	SM308C P30/865 L120W3 PSU WB WH	6500 K	98 lm/W	2,950 lm
52768399	SM308C P38/830 L140W3 PSU MB WH	3000 K	95 lm/W	3,610 lm
53157499	SM308C P38/830 L140W3 PSU WB WH	3000 K	95 lm/W	3,610 lm
53031799	SM308C P38/840 L140W3 PSU MB WH	4000 K	98 lm/W	3,750 lm
52526999	SM308C P38/840 L140W3 PSU WB WH	4000 K	98 lm/W	3,750 lm
52441599	SM308C P38/865 L140W3 PSU MB WH	6500 K	98 lm/W	3,750 lm
52606899	SM308C P38/865 L140W3 PSU WB WH	6500 K	98 lm/W	3,750 lm
52871099	SM308C P45/830 L170W3 PSU MB WH	3000 K	95 lm/W	4,300 lm
52352499	SM308C P45/830 L170W3 PSU WB WH	3000 K	95 lm/W	4,300 lm
52527699	SM308C P45/840 L170W3 PSU MB WH	4000 K	98 lm/W	4,410 lm
52442299	SM308C P45/840 L170W3 PSU WB WH	4000 K	98 lm/W	4,410 lm
52607599	SM308C P45/865 L170W3 PSU MB WH	6500 K	98 lm/W	4,410 lm
52872799	SM308C P45/865 L170W3 PSU WB WH	6500 K	98 lm/W	4,410 lm
52353199	SP308P P22/830 L75W3 PSU MB WH	3000 K	95 lm/W	2,090 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
52769099	SP308P P22/830 L75W3 PSU WB WH	3000 K	95 lm/W	2,090 lm
53158199	SP308P P22/840 L75W3 PSU MB WH	4000 K	98 lm/W	2,150 lm
53032499	SP308P P22/840 L75W3 PSU WB WH	4000 K	98 lm/W	2,150 lm
52528399	SP308P P22/865 L75W3 PSU MB WH	6500 K	98 lm/W	2,150 lm
52443999	SP308P P22/865 L75W3 PSU WB WH	6500 K	98 lm/W	2,150 lm
52770699	SP308P P30/830 L120W3 PSU MB WH	3000 K	95 lm/W	2,850 lm
53160499	SP308P P30/830 L120W3 PSU WB WH	3000 K	95 lm/W	2,850 lm
53034899	SP308P P30/840 L120W3 PSU MB WH	4000 K	98 lm/W	2,950 lm
52530699	SP308P P30/840 L120W3 PSU WB WH	4000 K	98 lm/W	2,950 lm
52445399	SP308P P30/865 L120W3 PSU MB WH	6500 K	98 lm/W	2,950 lm
52609999	SP308P P30/865 L120W3 PSU WB WH	6500 K	98 lm/W	2,950 lm
52876599	SP308P P38/830 L140W3 PSU MB WH	3000 K	95 lm/W	3,610 lm
52357999	SP308P P38/830 L140W3 PSU WB WH	3000 K	95 lm/W	3,610 lm
52773799	SP308P P38/840 L140W3 PSU MB WH	4000 K	98 lm/W	3,750 lm
53163599	SP308P P38/840 L140W3 PSU WB WH	4000 K	98 lm/W	3,750 lm
52612999	SP308P P38/865 L140W3 PSU MB WH	6500 K	98 lm/W	3,750 lm
52878999	SP308P P38/865 L140W3 PSU WB WH	6500 K	98 lm/W	3,750 lm
52359399	SP308P P45/830 L170W3 PSU MB WH	3000 K	95 lm/W	4,300 lm
52776899	SP308P P45/830 L170W3 PSU WB WH	3000 K	95 lm/W	4,300 lm
53167399	SP308P P45/840 L170W3 PSU MB WH	4000 K	98 lm/W	4,410 lm
53040999	SP308P P45/840 L170W3 PSU WB WH	4000 K	98 lm/W	4,410 lm
52536899	SP308P P45/865 L170W3 PSU MB WH	6500 K	98 lm/W	4,410 lm
52450799	SP308P P45/865 L170W3 PSU WB WH	6500 K	98 lm/W	4,410 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
53154399	SM308C P22/830 L75W3 PSU MB WH	22 W	53028799	SM308C P22/830 L75W3 PSU WB WH	22 W

Order Code	Full Product Name	Power Consumption
52524599	SM308C P22/840 L75W3 PSU MB WH	22 W
52440899	SM308C P22/840 L75W3 PSU WB WH	22 W
52605199	SM308C P22/865 L75W3 PSU MB WH	22 W
52869799	SM308C P22/865 L75W3 PSU WB WH	22 W
52350099	SM308C P30/830 L120W3 PSU MB WH	30 W
52767699	SM308C P30/830 L120W3 PSU WB WH	30 W
53156799	SM308C P30/840 L120W3 PSU MB WH	30 W
53030099	SM308C P30/840 L120W3 PSU WB WH	30 W
52870399	SM308C P30/865 L120W3 PSU MB WH	30 W
52351799	SM308C P30/865 L120W3 PSU WB WH	30 W
52768399	SM308C P38/830 L140W3 PSU MB WH	38 W
53157499	SM308C P38/830 L140W3 PSU WB WH	38 W
53031799	SM308C P38/840 L140W3 PSU MB WH	38 W
52526999	SM308C P38/840 L140W3 PSU WB WH	38 W
52441599	SM308C P38/865 L140W3 PSU MB WH	38 W
52606899	SM308C P38/865 L140W3 PSU WB WH	38 W
52871099	SM308C P45/830 L170W3 PSU MB WH	45 W
52352499	SM308C P45/830 L170W3 PSU WB WH	45 W
52527699	SM308C P45/840 L170W3 PSU MB WH	45 W
52442299	SM308C P45/840 L170W3 PSU WB WH	45 W
52607599	SM308C P45/865 L170W3 PSU MB WH	45 W
52872799	SM308C P45/865 L170W3 PSU WB WH	45 W
52353199	SP308P P22/830 L75W3 PSU MB WH	22 W

Order Code	Full Product Name	Power Consumption
52769099	SP308P P22/830 L75W3 PSU WB WH	22 W
53158199	SP308P P22/840 L75W3 PSU MB WH	22 W
53032499	SP308P P22/840 L75W3 PSU WB WH	22 W
52528399	SP308P P22/865 L75W3 PSU MB WH	22 W
52443999	SP308P P22/865 L75W3 PSU WB WH	22 W
52770699	SP308P P30/830 L120W3 PSU MB WH	30 W
53160499	SP308P P30/830 L120W3 PSU WB WH	30 W
53034899	SP308P P30/840 L120W3 PSU MB WH	30 W
52530699	SP308P P30/840 L120W3 PSU WB WH	30 W
52445399	SP308P P30/865 L120W3 PSU MB WH	30 W
52609999	SP308P P30/865 L120W3 PSU WB WH	30 W
52876599	SP308P P38/830 L140W3 PSU MB WH	38 W
52357999	SP308P P38/830 L140W3 PSU WB WH	38 W
52773799	SP308P P38/840 L140W3 PSU MB WH	38 W
53163599	SP308P P38/840 L140W3 PSU WB WH	38 W
52612999	SP308P P38/865 L140W3 PSU MB WH	38 W
52878999	SP308P P38/865 L140W3 PSU WB WH	38 W
52359399	SP308P P45/830 L170W3 PSU MB WH	45 W
52776899	SP308P P45/830 L170W3 PSU WB WH	45 W
53167399	SP308P P45/840 L170W3 PSU MB WH	45 W
53040999	SP308P P45/840 L170W3 PSU WB WH	45 W
52536899	SP308P P45/865 L170W3 PSU MB WH	45 W
52450799	SP308P P45/865 L170W3 PSU WB WH	45 W

