



Party Spot

13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF

Philips 13.5-watt PAR 38s provide bright colorful light perfect for special occasions, parties and holidays. These PAR 38 lamps are available in up to four different colors and offer a festive touch to your home lighting. Brighten up your home and celebrate with color using these energy saving LED bulbs.


Product data

General Information		Voltage (Nom) 120 V	
Cap-Base	E26 [Single Contact Medium Screw]	UL Type Yes	
Nominal lifetime	10,950 hour(s)	Temperature	
Switching Cycle	10,000	Ambient temperature range -4 °F to 113 °F	
Rated Lifetime (Hours)	10,950 hour(s)	T-Case Maximum (Nom) 149 °F	
Lighting Technology	LED	Controls and Dimming	
EU RoHS compliant	Yes	Dimmable No	
Light Technical		Mechanical and Housing	
Color Code	Yellow	Bulb Finish Frosted	
Color Designation	Yellow	Bulb Material Glass	
Color Consistency	<6	Bulb Shape PAR38	
Color rendering index (CRI)	-	UL Wet/ damp/ dry location Wet location	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
Operating and Electrical		Suitable For Accent Lighting Yes	
Line Frequency	60 Hz	EyeComfort Yes	
Input Frequency	60 Hz	T20 compliant N/A	
Power Consumption	13.5 W		
Lamp Current (Nom)	165 mA		
Starting Time (Nom)	0.5 s		
Warm-up time to 60% light	0.5 s		
Power Factor (Fraction)	0.5		


Party Spot

Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF
Full product name	13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF

Dimensional drawing




Photometric data



Light Distribution Diagram - 13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF


Order code	568279
Material Nr. (12NC)	929001306633
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677568276
Numerator - Packs per outer box	3
EAN/UPC - Case	50046677568271

Product	D	C
13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF	4-13/16 inch	5-1/4 inch




Accent Lighting Spots - 13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF

Lifetime



Lumen Maintenance Diagram - 13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF



Life Expectancy Diagram - 13.5PAR38/PER/YELLOW/G/E26/ND/ULW 3/1PF

