

Specialty Lamps

4A19/PER/RED/G/E26/ND 4/1PF

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

Product data


General Information		Starting Time (Nom)	
Cap-Base	E26 [Single Contact Medium Screw]	Warm-up time to 60% light	0.5 s
Nominal lifetime	15,000 hour(s)	Power Factor (Fraction)	0.40
Switching Cycle	20,000	Voltage (Nom)	120 V
Rated Lifetime (Hours)	15,000 hour(s)	Temperature	
Lighting Technology	LED	Ambient temperature range	-4 °F to 113 °F
EU RoHS compliant	Yes	T-Case Maximum (Nom)	257 °F
Light Technical		Controls and Dimming	
Color Code	Red	Dimmable	No
Beam Angle (Nom)	330 degree(s)	Mechanical and Housing	
Color Designation	Red	Bulb Finish	Red
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Material	Glass
Operating and Electrical		Bulb Shape	A19
Line Frequency	60 Hz	UL Wet/ damp/ dry location	Wet location
Input Frequency	60 Hz	Approval and Application	
Power Consumption	4 W	EyeComfort	Yes
Lamp Current (Nom)	55 mA		
Wattage Equivalent	40 W		

Specialty Lamps

T20 compliant	N/A
Application Conditions	
can it be used in closed luminaires	No
Product Data	
Order product name	4A19/PER/RED/G/E26/ND 4/1PF
Full product name	4A19/PER/RED/G/E26/ND 4/1PF


Order code	568832
Material Nr. (12NC)	929001937053
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677568832
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677568837

Dimensional drawing



Product	D	C
4A19/PER/RED/G/E26/ND 4/1PF	2-3/8 inch	4-3/16 inch

Photometric data



OSRAM Photometric 11 - All-in-One Lighting 11 - Page 11

Light Distribution Diagram - 4A19/PER/RED/G/E26/ND 4/1PF

General uniform lighting - 4A19/PER/RED/G/E26/ND 4/1PF

Specialty Lamps

Lifetime



Life Expectancy Diagram - 4A19/PER/RED/G/E26/ND 4/1PF

Lumen Maintenance Diagram - 4A19/PER/RED/G/E26/ND 4/1PF

