

# Specialty Lamps

## 4A19/PER/YELLOW/G/E26/ND 4/1PF

Philips A shape party lamp provides a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays. Philips Dusk to Dawn A19 lamp is equipped with a built-in light sensor that turns the lights on automatically when the sun goes down and turns the light off when the sun rises. Philips 3-Way A shape lamps provides omni-directional light perfect for general room lighting. This lamp creates a comfortable atmosphere by providing 3 wattage levels of soft, white light that will not fade fabrics or furnishings.

### Product data


<b>General Information</b>		<b>Starting Time (Nom)</b>		0.5 s
Cap-Base	E26 [Single Contact Medium Screw]	<b>Warm-up time to 60% light</b>		0.5 s
Nominal lifetime	15,000 hour(s)	<b>Power Factor (Fraction)</b>		0.40
Switching Cycle	20,000	<b>Voltage (Nom)</b>		120 V
Rated Lifetime (Hours)	15,000 hour(s)	<b>Temperature</b>		
Lighting Technology	LED	<b>Ambient temperature range</b>		-4 °F to 113 °F
EU RoHS compliant	Yes	<b>T-Case Maximum (Nom)</b>		257 °F
<b>Light Technical</b>		<b>Controls and Dimming</b>		
Color Code	Yellow	<b>Dimmable</b>		No
Beam Angle (Nom)	330 degree(s)	<b>Mechanical and Housing</b>		
Color Designation	Yellow	<b>Bulb Finish</b>		Yellow
LLMF At End Of Nominal Lifetime (Nom)	70 %	<b>Bulb Material</b>		Glass
<b>Operating and Electrical</b>		<b>Bulb Shape</b>		A19
Line Frequency	60 Hz	<b>UL Wet/ damp/ dry location</b>		Wet location
Input Frequency	60 Hz	<b>Approval and Application</b>		
Power Consumption	4 W	<b>EyeComfort</b>		Yes
Lamp Current (Nom)	55 mA			
Wattage Equivalent	40 W			

Specialty Lamps

T20 compliant	N/A
Application Conditions	
can it be used in closed luminaires	No
Product Data	
Order product name	4A19/PER/YELLOW/G/E26/ND 4/1PF
Full product name	4A19/PER/YELLOW/G/E26/ND 4/1PF


Order code	568857
Material Nr. (12NC)	929001937253
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677568856
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677568851

Dimensional drawing



Product	D	C
4A19/PER/YELLOW/G/E26/ND 4/1PF	2-3/8 inch	4-3/16 inch

Photometric data



General Uniform Lighting 1 x 40W/800lm LED Page 1/1

General uniform lighting - 4A19/PER/YELLOW/G/E26/ND 4/1PF

Light Distribution Diagram - 4A19/PER/YELLOW/G/E26/ND 4/1PF

Specialty Lamps

Lifetime



Life Expectancy Diagram - 4A19/PER/YELLOW/G/E26/ND 4/1PF



Lumen Maintenance Diagram - 4A19/PER/YELLOW/G/E26/ND 4/1PF

