



LEDLamps

LEDBulb 10.5-75W E27 2700K D 1PF/6 AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost


Product data

General Information			
Cap-Base	E27	Lamp Current (Nom)	55 mA
Nominal lifetime	15,000 hour(s)	Wattage Equivalent	75 W
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Rated Lifetime (Hours)	15,000 hour(s)	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.9
EU RoHS compliant	Yes	Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	927 [CCT of 2700K]	Ambient temperature range	-20 to +45 °C
Color Code	927 [CCT of 2700K]	T-Case Maximum (Nom)	90 °C
Beam Angle (Nom)	150 degree(s)	Controls and Dimming	
Luminous Flux	1,055 lm	Dimmable	Only with specific dimmers
Color Designation	Warm White (WW)	Mechanical and Housing	
Correlated Color Temperature (Nom)	2700 K	Bulb Finish	Frosted
Luminous Efficacy (rated) (Nom)	100 lm/W	Bulb Material	Plastic
Color Consistency	<6	Bulb Shape	A60
Color rendering index (CRI)	90	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Consumption kWh/1000 h	11 kWh
Operating and Electrical		EyeComfort	Yes
Input Frequency	50 to 60 Hz		
Power Consumption	10.5 W		

LED Innovations	EyeComfort
Product Data	
Order product name	LEDBulb 10.5-75W E27 2700K D 1PF/6 AU
Full product name	LEDBulb 10.5-75W E27 2700K D 1PF/6 AU
Full product code	871951433361100
Order code	929002069319



Material Nr. (12NC)	929002069319
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514333611
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514386990

Dimensional drawing




Product	D	C
LEDBulb 10.5-75W E27 2700K D 1PF/6 AU	60 mm	110 mm

Photometric data



Light Distribution Diagram - LEDBulb 10.5-75W E27 2700K D 1PF/6 AU

General uniform lighting - LEDBulb 10.5-75W E27 2700K D 1PF/6 AU



Spectral Power Distribution Colour - LEDBulb 10.5-75W E27 2700K D 1PF/6 AU

Lifetime



Life Expectancy Diagram - LEDBulb 10.5-75W E27 2700K D 1PF/6 AU



Lumen Maintenance Diagram - LEDBulb 10.5-75W E27 2700K D 1PF/6 AU

