



LEDLamps

LEDGlobe 10-75W G120 E27 WW 230V_AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data


General Information	
Cap-Base	E27
Nominal lifetime	15,000 h
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	1,055 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	105 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	10 W

Lamp Current (Nom)	75 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	50 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	G120
Approval and Application	
Energy Consumption kWh/1000 h	10 kWh
EyeComfort	Yes

LED Innovations	EyeComfort
Product Data	
Order product name	LEDGlobe 10-75W G120 E27 WW 230V_AU
Full product name	LEDGlobe 10-75W G120 E27 WW 230V_AU
Full product code	871869673242700
Local code description	G1201000LE27WW
Order code	929002442169


Material Nr. (12NC)	929002442169
Local order code	G1201000LE27WW
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696732427
Numerator - Packs per outer box	3
EAN/UPC - Case	8719514271593

Dimensional drawing




Product	D	C
LEDGlobe 10-75W G120 E27 WW 230V_AU	120 mm	170 mm


Photometric data



Spectral Power Distribution Colour - LEDGlobe 10-75W G120 E27 WW 230V_AU



General uniform lighting - LEDGlobe 10-75W G120 E27 WW 230V_AU



Light Distribution Diagram - LEDGlobe 10-75W G120 E27 WW 230V_AU

Lifetime



Life Expectancy Diagram - LEDGlobe 10-75W G120 E27 WW 230V_AU



Lumen Maintenance Diagram - LEDGlobe 10-75W G120 E27 WW 230V_AU

