



Classic filament LEDbulbs

LED CLA 40W A60 E27 4000K CL EELA SRT AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information			
Cap-Base	E27	Power Consumption	2.3 W
Nominal lifetime	50,000 hour(s)	Lamp Current (Nom)	30 mA
Switching Cycle	50,000	Wattage Equivalent	40 W
Rated Lifetime (Hours)	50,000 hour(s)	Starting Time (Nom)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	840 [CCT of 4000K]	Ambient temperature range	-20 to +45 °C
Color Code	840 [CCT of 4000K]	T-Case Maximum (Nom)	35 °C
Luminous Flux	485 lm	Controls and Dimming	
Color Designation	Cool White (CW)	Dimmable	No
Correlated Color Temperature (Nom)	4000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	210 lm/W	Bulb Finish	Clear
Color Consistency	<6	Bulb Material	Glass
Color rendering index (CRI)	80	Bulb Shape	A60
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
Photobiological safety according to EN 62471	RG1	Energy Consumption kWh/1000 h	- kWh
Operating and Electrical			
Input Frequency	50 to 60 Hz		

Classic filament LEDbulbs

EyeComfort	Yes
Product Data	
Order product name	LED CLA 40W A60 E27 4000K CL EELA SRT AU
Full product name	LED CLA 40W A60 E27 4000K CL EELA SRT AU
Full product code	871951445495800


Order code	929003066519
Material Nr. (12NC)	929003066519
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514454958
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514454965

Dimensional drawing




Product	D	C
LED CLA 40W A60 E27 4000K CL EELA SRT AU	60 mm	105 mm


Photometric data



Spectral Power Distribution Colour - LED CLA 40W A60 E27 4000K CL EELA SRT AU




Light Distribution Diagram - LED CLA 40W A60 E27 4000K CL EELA SRT AU




General uniform lighting - LED CLA 40W A60 E27 4000K CL EELA SRT AU

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LED CLA 40W A60 E27 4000K CL EELA SRT AU



Lumen Maintenance Diagram - LED CLA 40W A60 E27 4000K CL EELA SRT AU

