




Classic filament LEDbulbs

LEDclassic 60W B22 2700K G120 D CL AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data

General Information	
Cap-Base	B22
Nominal lifetime	15,000 h
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	927 [CCT of 2700K]
Color Code	927 [CCT of 2700K]
Luminous Flux	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	134 lm/W
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	6 W

Lamp Current (Nom)	35 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V

Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	80 °C

Controls and Dimming	
Dimmable	Only with specific dimmers

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	G120


Approval and Application	
Energy Consumption kWh/1000 h	6 kWh

Classic filament LEDbulbs

Product Data	
Order product name	LEDclassic 60W B22 2700K G120 D CL AU
Full product name	LEDclassic 60W B22 2700K G120 D CL AU
Full product code	871951438590000
Local code description	FIL60WG120WWBCD
Order code	929003100779
Material Nr. (12NC)	929003100779



Local order code	FIL60WG120WWBCD
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514385900
Numerator - Packs per outer box	3
EAN/UPC - Case	8719514385917

Dimensional drawing




Product	D	C
LEDclassic 60W B22 2700K G120 D CL AU	124 mm	178 mm

Photometric data



General uniform lighting - LEDclassic 60W B22 2700K G120 D CL AU


Light Distribution Diagram - LEDclassic 60W B22 2700K G120 D CL AU




Spectral Power Distribution Colour - LEDclassic 60W B22 2700K G120 D CL AU

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LEDclassic 60W B22 2700K G120 D CL AU



Lumen Maintenance Diagram - LEDclassic 60W B22 2700K G120 D CL AU

