

Classic filament LEDbulbs

LED CLA 40W A60 B22 3000K CL EELA SRT AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information		Power Consumption	
Cap-Base	B22		2.3 W
Nominal lifetime	50,000 h	Lamp Current (Nom)	30 mA
Switching Cycle	50,000	Wattage Equivalent	40 W
Rated Lifetime (Hours)	50,000 h	Starting Time (Nom)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.4
Light Technical		Voltage (Nom)	220-240 V
Color Code	830 [CCT of 3000K]	Temperature	
Color Code	830 [CCT of 3000K]	Ambient temperature range	-20 to +45 °C
Luminous Flux	485 lm	T-Case Maximum (Nom)	35 °C
Color Designation	White (WH)	Controls and Dimming	
Correlated Color Temperature (Nom)	3000 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	210 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Clear
Color rendering index (CRI)	80	Bulb Material	Glass
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	A60
Photobiological safety according to EN 62471	RG1	Approval and Application	
Operating and Electrical		Energy Consumption kWh/1000 h	- kWh
Input Frequency	50 to 60 Hz		

Classic filament LEDbulbs

EyeComfort	Yes
LED Innovations	UltraEfficient EyeComfort
Product Data	
Order product name	LED CLA 40W A60 B22 3000K CL EELA SRT AU
Full product name	LED CLA 40W A60 B22 3000K CL EELA SRT AU
Full product code	87195144582200


Order code	929003539719
Material Nr. (12NC)	929003539719
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514458222
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514458239

Dimensional drawing




Product	D	C
LED CLA 40W A60 B22 3000K CL EELA SRT AU	60 mm	105 mm


Photometric data



Spectral Power Distribution Colour - LED CLA 40W A60 B22 3000K CL EELA SRT AU




Light Distribution Diagram - LED CLA 40W A60 B22 3000K CL EELA SRT AU




Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LED CLA 40W A60 B22 3000K CL EELA SRT AU



Lumen Maintenance Diagram - LED CLA 40W A60 B22 3000K CL EELA SRT AU

