



## Flex Strip 32.8ft

Craft mesmerizing shapes with Smart Flex Strip's bendable design, adding flair to any room. With its vibrant colors and effects, you can effortlessly set the perfect mood for any occasion. Whether through the WiZ App, voice commands, or remote control, personalizing your lighting experience has never been easier. Transform your living space effortlessly and sculpt light in ways you never thought possible with Smart Flex Strip.

## PRODUCT HIGHLIGHTS

- Full color
- Low Voltage
- IP20/Silicon



### Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



### Matter Certified

This product is Matter certified. You can set it up and control it with your preferred smart home platform and make it work seamlessly with other Matter Certified devices.



### Exclusive SpaceSense™ light that turns on with movement

WiZ's SpaceSense technology turns your lights into motion sensors. With a minimum of two WiZ lights in a room, you can activate the SpaceSense feature in the WiZ app and have lights turn on and off automatically with motion detection. It's simple. It's SpaceSense. It's WiZ.



### Millions of colors and changing light modes to make your day

Choose any light color you like or simply apply a dynamic light mode we designed for you. Fireplace or Ocean, for example, will help you create an amazing atmosphere and lift your mood.



### Sync Lights to Music

Dive into the rhythm with our Music Sync feature. Effortlessly synchronize your lights to your favorite tunes. Just remember, keep your mobile device near the speaker for perfect harmony between sound and light.



### Gradient colors in a single strip

Set the mood with flexible light strips that offer gradient effects. Dynamic light modes let you create the right ambience for beautifying any room.



# SPECIFICATIONS

## BULB CHARACTERISTICS

Intended use: Indoor

## DESIGN AND FINISHING

Color: White

Material: Plastic

## DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)

Lumen maintenance factor: 70%

Nominal lifetime: 15,000

Number of switch cycles: 50,000

## EXTRA FEATURE/ACCESSORY INCL.

Dimmable with remote control: Yes

LED integrated: Yes

On/off switch on wire: Yes

Power adapter included: Yes

Remote control included: No

## LIGHT CHARACTERISTICS

Color rendering index (CRI): -

Warm-up time to 60% light: <2

## STRING LIGHT/LIGHTSTRIP

Output Power: 39.5 W

## MISCELLANEOUS

Especially designed for: Ambience

## OTHER CHARACTERISTICS

Lamp current: 715 mA

## POWER CONSUMPTION

Power factor: 0.45

Voltage: 120 V

## PRODUCT DIMENSIONS AND WEIGHT

Net weight: 1.27 kg

Height: 1.3 cm

Length: 1,000 cm

Width: 0.6 cm

## SERVICE

Warranty: 2 year(s)

Subscription: Not applicable

## TECHNICAL SPECIFICATIONS

Total lumen output fixture: NA

Light color: RGB

Fixture dimmable: Wireless Dim - Do not use with dimmer

Wattage bulb included: 45

IP code: IP20 | Finger-protected

Class of protection: Class II - Double Insulated

## WHAT'S SUPPORTED

Max. number of accessories: 9999

Compatible with Effects: Yes

WiFi: Wireless G

Defined support period: Minimum of 60 months after introduction date

Communication protocol: Bluetooth WiFi (2.4GHz)

## PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677605612

Net weight: 1.27 kg

Gross weight: 1.58 kg

Height: 9.3 cm

Length: 23.7 cm

Width: 23.7 cm



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.