

## HF-Selectalume II for TL5 lamps

#### HF-S 154 TL5 II 220-240V 50/60Hz

HF-Selectalume II TL5 is the most cost-effective, reliable and outstanding solution for fluorescent lamps. These ballasts are part of an overall high-efficiency lighting system that may help you or your customers to achieve any international or local energy code you need to comply with. HF-Selectalume II TL5 ballasts are the ideal choice for a broad range of new construction and retrofit applications within the commercial sector, including general surface mounting or office lighting, parking garages, warehouses, waterproof and other applications.

#### Product data

#### • General Characteristics

Application code Rated Lamptype TL5 Rated Number of 1 piece Lamps 54

Rated Ballast-Lamp

Power

Line Voltage 220-240 V Line Frequency 50/60 Hz L 280x30x21 Housing

Energy Efficiency Index

Lifetime 90% 50000 hr

surv.@Tcaselife

#### • Operating Characteristics

Automatic restart Preheat time 1.6 s 40-60 kHz Operating frequency

Mains voltage safety

198-264V -10%/+10%

20 (max) A

0.5 (max) mA

0.25 ms

(AC)

Mains voltage 202-254V -8%/+6% performance (AC)

Inrush current Peak Inrush current Width Earth leakage current Power losses gear

4.7 W 1.02 -Ballast Lumen Factor PowerFactor 100% 0.98 output power

Overvoltage protection 320Vac Overvoltage protection 350Vac

Crestfactor

48 hr 2 hr 1.7 -

Hum and Noise level

< 30 dB(A)

 Wiring Characteristics Cable-Cap output-200 (max) pF

wires mutual WAGO 744 connector Conn.type input

terminals Conn.type output WAGO 744 connector [Suitable for

terminals manual wiring] Max. cable length 0.75 m

Hot Wires Striplength

8.0-9.0 mm Dual fixture Master/ Possible, lamp wires 2m max. length [Master/Slave operation possible]

0.50-1.50 mm2 Wcs Input terminals Wcs Output termi-0.50-1.50 mm2

nals

Cable-Cap hot outwires-earth

Cable-Cap cold out-200 (max) pF

wires-earth

200 (max) pF

#### • System Chars on driver level

Rated Lamp Power 54 on TL5 58.7 System Power on TL5 Lamp Power on TL5 Power Loss on TL5

#### • Temperature Characteristics

F-marking Yes T-case life 75 C 75 (max) C T-case maximum



### HF-Selectalume II for TL5 lamps

-15 (min), 50 (max) C T-ambient -40 (min), 80 (max) C T-storage

#### • Emergency Characteristics

Bal Lm Fac Emergency operation

50% of EBLF Light output after 5

Light output after 60 100% of EBLF

sec

Normal operating 220-240 V voltage (DC) Batt volt guaranteed 186-275 V

ignition

Batt volt guaranteed

operation

176-275 V

#### • Product Dimensions

Length A1 280 mm Fixing Hole Distance 265 mm Length A2 Width B1 30.0 mm Height C1 28.0 mm Fixing Hole Diameter 4.1 mm

#### • Approval & Application Chars

EMI 9kHz .. 30 MHz EN 55015

#### IEC 68-2-6 Fc Vibrations

IEC 68-2-29 Eb (10G/16ms) **Bumps** CE / CCC / ENÈC / VDE-EMV Approval marks

CE marking ENEC certificate Yes C-Tick certificate Yes CCC certificate Yes PSB certification Yes TISI marking Yes SIRIM approval Yes CB Certificate Yes

#### • Product Data

Order code 913713033666 913713033666 Full product code

HF-S 154 TL5 II 220-240V 50/60Hz Full product name HF-S 154 TL5 II 220-240V 50/60Hz Order product name

Pieces per pack Packing configuration 12 Packs per outerbox 12

8711500999375 Bar code on pack -

EAN1 Bar code on outerbox - EAN3

Logistic code(s) -


12NC

Net weight per piece

8727900905618 913713033666


0.185 kg

#### Dimensional drawing



#### HF-S 154 TL5 II 220-240V 50/60Hz

Product	A1 (Norm)	A2 (Norm)	B1 (Norm)	C1 (Norm)	D1 (Norm)
HF-S 154 TL5 II 220-240V 50/60Hz	280	265	30.0	28.0	4.1



Photometric data

# Ballast type

HF-S 154 TL5 II 220-240V 50/60Hz

