


DMNG232 RS232 Network Gateway

Cost-effective serial port integration

The Philips Dynalite DMNG232 network gateway provides cost-effective serial port integration between a DyNet network and third-party systems.

- Seamless integration with third-party systems
 — Including AV systems, lighting desks, data projectors, HVAC, BMS and security systems.
- Internal controls Including programmable logic controller capable of comprehensive conditional and sequential logic and arithmetic function processing.
- Utilize data format library or create your own — A library of data formats is available for systems integrators, or can be created using the onboard conditional logic engine to assemble and transmit user-defined data strings.
- Macro functions available To simplify the control of multiple devices.
- Powered from the DyNet network Requires no mains voltage supply.



For detailed product information, please refer to the product information pages at www.philips.com/dynalite and follow the links.




Specifications

Due to continuous improvements and innovations, specifications may change without notice.

| Item | Specification | Details |
|-------------------|-------------------------|---|
| Electrical | Input Voltage | 15 VDC supplied by the DyNet network @ 50 mA |
| Control | Control Ports | One RS-485 DyNet serial port One RS-232 serial port |
| | RS-485 Port Connections | SHLD, GND, D-, D+, +12 V All available on screw terminals 1 \times 2.5 mm 2 max conductor size. Also available on RJ12 socket |
| | RS-232 Port Connections | Female DB9 connection |
| | RS-232 Port Modes | DTE, DCE; selected by jumpers |
| | RS232 Data Formats | Baudrate: 600 - 250 k Max packet length: 254 bytes Data bits: 7 / 8 Stop bits: 1 / 2 Parity: odd/even/none Flow control: none / RTS-CTS |
| | User Controls | Service Switch Diagnostic LED |
| | Internal Controls | Programmable Logic Controller |
| Physical | Dimensions (H x W x D) | 37 mm x 79 mm x 149 mm (1.4" x 3.1" x 5.9") |
| | Packed Weight | 0.15 kg |
| | Construction | ABS plastic |
| | Operating Conditions | Temperature: 0 to 50° C ambient Humdity: 0 to 95% non-condensing |
| | Storage & Transport | Temperature: -25 to 60° C ambient Humidity: 0 to 90% non-condensing |
| Certification | Certification | CE, C-Tick |
| Options & Ordeing | Standard Product | DMNG232 (Philips 12NC - 913703080309) |

Electrical Diagram





RS-232 Control Lines

| Pin | Function | Implementation |
|-----|---------------------------|---------------------|
| 1 | DCD (data carrier detect) | Not conected |
| 2 | RD (received data) | Connected to UART |
| 3 | TD (transmitted data) | Connected to UART |
| 4 | DTR (data terminal ready) | Not conected |
| 5 | SG (signal ground) | Connected to Ground |
| 6 | DSR (data set ready) | Not connected |
| 7 | RTS (request to send) | Software controlled |
| 8 | CTS (clear to send) | Software controlled |
| 9 | RI (ring indicator) | Not connected |



Philips Dynalite 6 / 691 Gardeners Road Mascot, NSW 2020 Australia

Tel: +61 2 8338 9899

Email: dynalite.info@philips.com Web: www.philips.com/dynalite Specifications subject to change without notice. © WMGD Pty LtdTrading as Dynalite. Unit 6, 691 Gardeners Road Mascot 2020 Australia. ABN 33 097 246 921. All rights reserved. Dynalite, DyNet and associated logos are the registered trademarks of WMGD Pty Ltd. Not to be reproduced without permission.