

# PHILIPS Day-Brite CFI

Recessed

T-Grid LED  
troffer 2x2

2000, 3000, 3800 or  
4500 lumens



Project: \_\_\_\_\_  
Location: \_\_\_\_\_  
Cat.No: \_\_\_\_\_  
Type: \_\_\_\_\_  
Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
Notes: \_\_\_\_\_

The Philips Day-Brite / Philips CFI T-Grid LED troffer is an energy efficient low profile luminaire offering excellent performance for general lighting applications such as offices, schools, healthcare, or retail. Featuring a frosted prismatic lens to enhance visual comfort, the T-Grid LED Troffer utilizes highly reliable and efficient Philips LED platform boards and dimmable driver, enabling market leading efficiency in its category.

## Ordering guide

Example: 2TG30L840-2-FS-02F-UNV-DIM

Width	Family	Ceiling Type	Lumen Package	Color Temp.	Length	Door Frame	Lens	Voltage	Driver	Options
2	T	G		—	2 —	—	02F —	—	—	
2 2'	T T-Grid LED troffer	G Grid	20L 2000 nominal delivered lumens 30L 3000 nominal delivered lumens 38L 3800 nominal delivered lumens 45L 4500 nominal delivered lumens	830 80 CRI, 3000K 835 80 CRI, 3500K 840 80 CRI, 4000K 850 80 CRI, 5000K	2 2'	FS Flat Steel FA Flat Aluminum RA Regressed Aluminum	02F Pattern 12, .100" nominal diffuse 50%	UNV Universal Voltage 120-277V 347 347V	DIM 0-10V dimming SDIM Step dimming to 40% input power	F1 3/8" flex, 3 wire, 18 gauge 6' F2 3/8" flex, 4 wire, 18 gauge 6' F1/D 3/8" twin flex, 3 wire, 18 gauge 6', for dimmable luminaires F2/SW 3/8" single flex, 5 wire, 18 gauge 6', for dimmable luminaires EMLED <sup>1</sup> Integral emergency battery pack 1W 1-way gasket between lens & door frame (not avail. for RA door frame) 2W 1-way & gasket between door frame & housing 3W 2-way & gasket between housing & ceiling (field installed) GLR Fusing, fast blow CHIC Chicago Plenum rated

## Footnotes

1 Emergency pack mounted in enclosure on top of fixture housing. Delivers 1100 nominal lumens in DC mode.

## Accessories (order separately)

- FMA22 – 2'x2' "F" mounting frame for NEMA "F" mounting
- FKTG822 – Flange conversion kit, 2'x2'



# 2TG T-Grid LED troffer 2x2

2000, 3000, 3800 or 4500 lumens

## Application

- High efficacy long life solid state lighting platform.
- General lighting distribution is excellent for ambient lighting.
- High CRI source provides excellent color rendering.
- LEDs are an excellent source for use with controls since frequent switching does not affect the life of the light source.

## Construction/finish

- A quality low-profile troffer with specification features for NEMA "G" grid, NEMA "NFC" narrow face grid, NEMA "GR" grid regressed, or NEMA "F" flange ceiling types.
- 3" nominal housing depth, 3-3/16" maximum depth.
- Smooth rolled edges on all four sides for easy handling.
- Die-formed one piece housing includes stiffening embosses and provides increased rigidity.
- Housing is multi-stage phosphate treated for maximum corrosion resistance and finish coat is high reflectance baked white enamel.
- Integral baffling system to prevent light leaks.
- 2 sets of integral grid clips (wraparound and fold-out) for maximum mounting flexibility.

- Integral wire hanger holes for independent wire suspension.
- Embosses with holes provided in housing end for screwing to T-bar if desired.
- 7/8" K.O.'s provided in each end cap for through wiring.
- Factory installed access plate in housing top includes 7/8" hole with rolled edge and 7/8" K.O.
- Carton includes integral carrying handle for easy handling.

## Electrical


- Standard 0-10V dimming.
- Driver and LED boards are accessible from below. LED boards are individually replaceable if required.
- Five-year luminaire limited warranty including LED boards and driver. Visit [www.philips.com/warranties](http://www.philips.com/warranties) for complete warranty information.
- High efficiency LEDs have 50,000 hour rated life (defined by testing at 70% lumen maintenance (L70)), based on 25°C ambient operating temperature.
- cETLus listed to UL and CSA standards, suitable for damp location.
- T-Grid LED luminaires are DesignLights Consortium® qualified. Please see the DLC QPL list for exact catalog numbers (<http://www.designlights.org/QPL>).

- Many luminaire components, such as reflectors, refractors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.



## Enclosure

- Full "C" channel door frames for improved lens support and reduced shipping damage.
- Flat steel door frame features smooth rolled edges inside and outside.
- All door frames have mitered corners.
- All door frames use T-hinges and can be hinged and latched from either side.
- Opposable spring loaded latches are standard for easy operation and consistent retention.

## Dimensions



\*EMLED option adds 1-3/4" to overall height



Fold-Out Grid Clips




# 2TG T-Grid LED troffer 2x2

2000, 3000, 3800 or 4500 lumens

## Photometry




### 2x2 T-Grid LED troffer, 2000 nominal delivered lumens

LER – 99

Catalog No.	2TG20L840-2-FS-02F-UNV	Candlepower				Light Distribution			Average Luminance			
		Angle	End	45	Cross	Degrees	Lumens	% Luminaire	Angle	End	45°	Cross
Test No.	32630	0	983	983	983	0-30	747	32.7	45	2442	2472	2551
S/MH	1.2	5	978	978	979	0-40	1191	52.1	55	1968	1977	2058
Source	LED	15	933	935	937	0-60	1915	83.7	65	1572	1518	1644
Lumens/Lamp	2287	25	844	849	856	0-90	2287	100.0	75	1427	1384	1618
Input Watts	23	35	703	709	709				85	1570	1597	1831
		45	526	532	549							
		55	344	345	359							
		65	202	195	211							
		75	112	109	127							
		85	42	42	49							
Comparative yearly lighting energy cost per 1000 lumens – <b>\$2.42</b> based on 3000 hrs. and \$.08 pwr KWH. Actual rates and usage may vary.												
The photometric results were obtained in the Philips Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.												
Photometric values based on test performed in compliance with LM-79.												

### 2x2 T-Grid LED troffer, 3000 nominal delivered lumens

LER – 92

Catalog No.	2TG30L840-2-FS-02F-UNV	Candlepower				Light Distribution			Average Luminance			
		Angle	End	45	Cross	Degrees	Lumens	% Luminaire	Angle	End	45°	Cross
Test No.	32628	0	1285	1285	1285	0-30	977	32.7	45	3201	3234	3342
S/MH	1.2	5	1279	1279	1281	0-40	1558	52.0	55	2575	2589	2694
Source	LED	15	1220	1223	1228	0-60	2506	83.7	65	2052	1992	2153
Lumens/Lamp	2994	25	1104	1110	1122	0-90	2994	100.0	75	1865	1803	2124
Input Watts	32.7	35	921	926	947				85	2063	2092	2395
		45	689	696	719							
		55	449	452	470							
		65	264	256	277							
		75	147	142	167							
		85	55	56	64							
Comparative yearly lighting energy cost per 1000 lumens – <b>\$2.61</b> based on 3000 hrs. and \$.08 pwr KWH. Actual rates and usage may vary.												
The photometric results were obtained in the Philips Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.												
Photometric values based on test performed in compliance with LM-79.												

# 2TG T-Grid LED troffer 2x2

2000, 3000, 3800 or 4500 lumens

## Photometry

### 2x2 T-Grid LED troffer, 3800 nominal delivered lumens

LER – 85

Catalog No.	2TG38L840-2-FS-02F-UNV	Candlepower				Light Distribution			Average Luminance			
		Angle	End	45	Cross	Degrees	Lumens	% Luminaire	Angle	End	45°	Cross
Test No.	32631	0	1586	1586	1586	0-30	1206	32.7	45	3942	3990	4130
S/MH	1.2	5	1578	1578	1580	0-40	1922	52.0	55	3177	3193	3330
Source	LED	15	1505	1509	1514	0-60	3091	83.7	65	2534	2456	2660
Lumens/Lamp	3693	25	1362	1369	1384	0-90	3693	100.0	75	2301	2219	2625
Input Watts	43.5	35	1136	1143	1169				85	2545	2588	2951
		45	848	859	889							
		55	555	557	581							
		65	326	316	342							
		75	181	175	207							
		85	68	69	78							

Comparative yearly lighting energy cost per 1000 lumens – **\$2.82** based on 3000 hrs. and \$.08 pwr KWH. Actual rates and usage may vary.

The photometric results were obtained in the Philips Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.

Photometric values based on test performed in compliance with LM-79.

### 2x2 T-Grid LED troffer, 4500 nominal delivered lumens

LER – 88

Catalog No.	2TG45L840-2-FS-02F-UNV	Candlepower				Light Distribution			Average Luminance			
		Angle	End	45	Cross	Degrees	Lumens	% Luminaire	Angle	End	45°	Cross
Test No.	32395	0	1968	1968	1968	0-30	1489	32.7	45	4852	4887	5031
S/MH	1.2	5	1958	1957	1960	0-40	2366	52.0	55	3959	3952	4127
Source	LED	15	1864	1867	1873	0-60	3805	83.6	65	3202	3111	3327
Lumens/Lamp	4551	25	1677	1687	1702	0-90	4550	100.0	75	2872	2789	3167
Input Watts	51.5	35	1392	1401	1428				85	3038	3066	3468
		45	1044	1052	1083							
		55	691	690	720							
		65	412	400	428							
		75	226	220	250							
		85	81	81	92							

Comparative yearly lighting energy cost per 1000 lumens – **\$2.79** based on 3000 hrs. and \$.08 pwr KWH. Actual rates and usage may vary.

The photometric results were obtained in the Philips Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.

Photometric values based on test performed in compliance with LM-79.

© 2015 Koninklijke Philips N.V. All rights reserved.  
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.  
philips.com/luminaires



Philips Lighting, North America Corporation  
200 Franklin Square Drive, Somerset, NJ 08873  
Tel. 855-486-2216

Philips Lighting Canada Ltd.  
A division of Philips Electronics Ltd.  
281 Hillmount Rd, Markham, ON, Canada L6C 2S3  
Tel. 800-668-9008