

The Philips logo is displayed in white capital letters on a blue rectangular background.

MASTER LEDspot

CRI90



Spot on for color enhancement

With a high color rendering index of 90, the MASTER LEDspot MV is the perfect halogen replacement for retail applications. The single optics outshine other lamps with high intensity, high quality light that brings out the true colors in merchandise for an extra-long lifetime of 50,000 hours. Choose 4-35W or 5.4-50W in three color temperatures, all with high performance dimming and low energy consumption. So you can light up merchandise with LED.





MASTER LEDspot MV CRI90 SO



Product type	LED	Traditional	Lumen output	Efficacy	Beam intensity	Beam angle	CRI	Color temperature	EOC
MASTER LEDspot MV 4-35W	W	W	lm	lm/W	cd	°		K	8718696
D 4-35W GU10 927 25D	4	35	250	63	925	25	90	2700	45727600
D 4-35W GU10 930 25D	4	35	260	65	962	25	90	3000	45731300
D 4-35W GU10 940 25D	4	35	282	71	1040	25	90	4000	45735100
D 4-35W GU10 927 40D	4	35	262	66	560	40	90	2700	45729000
D 4-35W GU10 930 40D	4	35	272	68	582	40	90	3000	45733700
D 4-35W GU10 940 40D	4	35	285	71	624	40	90	4000	45739900

MASTER LEDspot MV 5.4-50W	W	W	lm	lm/W	cd	°		K	8718696
D 5.4-50W GU10 927 25D	5.4	50	360	80	1350	25	90	2700	45715300
D 5.4-50W GU10 930 25D	5.4	50	360	80	1350	25	90	3000	45719100
D 5.4-50W GU10 927 40D	5.4	50	378	84	800	40	90	2700	45717700
D 5.4-50W GU10 930 40D	5.4	50	378	84	800	40	90	3000	45721400
D 5.4-50W GU10 940 40D	5.4	50	392	87	830	40	90	4000	45725200

