



Ordering 12NC	9290 014 27606
Brand Name	CertaDrive
Description	CertaDrive 17W 400mA 240V
Model Number	C017C040V042FNP4AI
Input Voltage	220 - 240V
Input Frequency	50 Hz
RoHS	Yes
Approbations	IS 15885 (Part 2 / Sec 13)
Status	BIS Certified


Output	Output	Output	Efficiency	Max Case	Input	Max Input		THD @	Power	Surge	Weight	Envir.
Power	Voltage	Current	at Max Load	Temp	Current	Power	Isolation	Max Load	Factor	Protection		Protection
(W)	(V DC)	(A DC)		(°C)	(Arms)	(W)	(Input - Output)	(%)	@Max Load	(KV)	(Kg)	Rating
17	30 - 42	0.400	240V	75	240V	19	Isolated Driver	≤ 55 @Max	≥ 0.8	2	0.04	IP 20
			85		0.095			Load				Indoor use







Ordering 12NC	9290 014 27606
Brand Name	CertaDrive
Description	CertaDrive 17W 400mA 240V
Model Number	C017C040V042FNP4AI
Input Voltage	220 - 240V
Input Frequency	50 Hz
RoHS	Yes
Approbations	IS 15885 (Part 2 / Sec 13)
Status	BIS Certified



Produ	ot Data			
Full product code	9290 014 27606			
Full product name	CertaDrive 17W 400mA 240V			
Net weight per piece	40 gms			
Dimming	None (FIXED)			
Ambient Temp. Range	0°C to + 40°C			
Line Voltage (AC Nominal)	220 - 240V +/-10%			
Line Voltage (AC Performance Range)	170 - 270V			
Line Current	0.090A @ 240V			
Line Frequency	50 Hz			
Envir. Protection Rating	IP 20 (For Indoor use only)			
Life at Tc 75 drgree C	30000 hrs (nom.)			
Tc - Max.	75°C			
Input Over Voltage	Can Survive input Voltage Stress of 320V for 48 hours			
	Can Survive input Voltage Stress of 350V for 2 hours			
LED Current Tolerance	+/- 10%of Imax			
THD Total	≤ 55% @ Full Load @ 240V Supply			
P.F. at Max. Load	≥ 0.8			
Isolation (Input - Output) Isolated				
Protection	Short Circuit and Open Circuit Protection for LED + and LED -			
Standby Power	≤0.5W			



	,
Ordering 12NC	9290 014 27606
Brand Name	CertaDrive
Description	CertaDrive 17W 400mA 240V
Model Number	C017C040V042FNP4AI
Input Voltage	220 - 240V
Input Frequency	50 Hz
RoHS	Yes
Approbations	IS 15885 (Part 2 / Sec 13)
Status	BIS Certified

Installation & Application Notes:

Section I - Physical Characteristics

- 1.1 LED Driver shall be installed inside an electrical enclosure
- 1.2 Wiring inside electrical enclosure shall comply with 600V/105 °C rating or higher

Section II - Performance

- 2.1 LED Driver has a rated lifetime of 30,000 hours @ Tc ≤ 75°C
- 2.2 LED Driver tolerates sustained open circuit and short circuit output conditions without damage
- 2.3 LED Driver maximum allowable case temperature is 75°C see product label for measurement location
- 2.4 LED Driver complies with the requirements of IS 15885 (Part 2 / Sec 13)

ELECTRICAL RATINGS:

	Input, 50 Hz		Output (nominal)		
Model	V	Α	V DC	A DC	Watts
CertaDrive 17W 400mA 240V	220 - 240	0.095	30 - 42	0.400	17

TECHNICAL CONSIDERATIONS (NOT FOR FIELD REPRESENTATIVES USE):

Section III - Conditions of acceptability

When installed in the end-use equipment, the following are among the considerations to be made :

- 3.1 The equipment shall be installed in compliance with the enclosure, mounting, spacing, casualty and segregation requirements of the ultimate application.
- 3.2 The driver is suitable for indoor application only.
- 3.3 When the drivers are installed in the end-use application, the case temperature should not exceed the temperature limits specified in the following table:

Model	Input Voltage, Hz	Max Case @ TC , °C		
CertaDrive 17W 400mA 240V	220 - 240 , 50	75		