


# Installation instructions

Instructions de montage  
Montageanleitung  
Montage instructie

Instrucciones de montaje  
Instruções de montagem  
Monteringsinstruktioner  
Monteringsvejledning


Kokoonpano- ja kiinnitysohjeet  
Montaj yönergeleri  
Instrukcja montażu  
Οδηγίες συναρμολόγησης

Szerelési utasítások  
Návod k montáži  
Návod k montáži  
ИНСТРУКЦИЯ ПО МОНТАЖУ





		A	B	C	T° K	P max	
DN560B DN561B	LED8S	250 mm	550 mm	≥3 mm	830	9,1 W	0,72 kg
					840	9,1 W	
					827	12,7 W	
	LED12S	250 mm	550 mm	≥3 mm	830	12,9 W	
					840	12,9 W	
					930	12,7 W	

		A	B	C	T° K	P max	
DN570B DN571B	LED12S	300 mm	700 mm	≥3 mm	830	14 W	1,17 kg
					840	14 W	
					830	23,5 W	
	LED20S	300 mm	700 mm	≥3 mm	840	22 W	
					830	28,5 W	
					840	26,5 W	




	H	D	Ø
DN560B	72 mm	146 mm	164 mm
DN561B	86 mm	146 mm	164 mm
DN570B	96,5 mm	196 mm	214 mm
DN571B	119 mm	196 mm	214 mm




DN560/561 Ø150 ±2mm  
DN570/571 Ø200 ±2mm


1a




1b








1d



1c








1e



C2-C4-C6KW




C1KBST2 DALI




Dali dimming range  
1/100%

	XITANIUM 17W LH 0.3-1A 24V I 230V	XITANIUM 17W LH 0.3-1A 24V TD/Is 230V	XITANIUM 20W LH 0.15-0.5A 48V Is 230V	XITANIUM 20W LH 0.15-0.5A 48V TD/Is 230V	XITANIUM 25W 0.3-1 A 36V I230V	XITANIUM 25W 0.3-1A 36V TD/Is 230V
Electrical Characteristics	Electrical Characteristics	Electrical Characteristics	Electrical Characteristics	Electrical Characteristics	Electrical Characteristics	Electrical Characteristics
✓	✓	✓	✓	✓	✓	✓
Inom (A)	0.15	0.11	0.12	0.11	0.2	0.2
Imax (A)	8	20	18	16	8	20
Tref (μs)	180	150	240	220	180	150
MCB	Nr. Drivers Max		Nr. Drivers Max		Nr. Drivers Max	
B-10A	x15	x18	x20	x15	x15	x18
B-16A	x24	x30	x32	x24	x24	x30
C-10A	x24	x31	x33	x24	x24	x31
C-16A	x40	x51	x54	x40	x40	x51

## DN560B/561B/570B/571B + PG DN560B/561B/570B/571B + PGO




ZBS260 OCS.



Chiffon doux  
Soft cloth  
Weiches Tuch  
Zacht doekje  
Panno morbido  
Tejido Suave  
Blødt stykke stof  
Pehmeá kangas  
Miekká sciereczka  
Páno macio

## EL Version

DN560B / DN561B		DN570B / DN571B		
LED8S	LED12S	LED12S	LED20S	LED24S
Flux NP		Flux NP		
886 lm	960 lm	1110 lm	1900 lm	2200 lm
Flux P		Flux P		
886 lm	960 lm	1110 lm	1900 lm	2200 lm



**DALI drivers:** With DC supply the current output decrease to 15% → **Setting can be changed by customer.**

**Drivers DALI:** En Alimentation DC, courant de sortie limité à 15% → **Modifiable par l'installateur.**


**DALI drivers:** De uitgangsstroom wordt 15% lager op DC voeding → **Kan worden aangepast door de klant.**

**Equipos DALI:** Con DC alimentación, salida de corriente de 15% menos → **Ajuste necesita ser cambiado por el cliente.**


**DALI drivers:** Met DC leveren de huidige output daling tot 15% → **Instelling nodig hebben door de klant worden gewijzigd.**

## RIMLESS Version

### RIM Accessory




	H	Ø
DN560B	74 mm	139,5 mm
DN561B	88 mm	139,5 mm
DN570B	98,5 mm	189 mm
DN571B	121 mm	189 mm




**DN560/561** Ø150 ±2mm

**DN570/571** Ø200 ±2mm


1a



1b



2a





2b



2c



2d



**DN570B-DN571B LED24S 4000K** : Groupe de risque 1 suivant la norme IEC 62471:2006 / Risk group 1 according to IEC 62471:2006