


PHILIPS

Coreline Recessed



RC134B / RC135B



RC134B W60L60
RC135B W62L62



RC134B W30L120



Safety cable
1x



220V
240V

50Hz
60Hz



LEDs


IP44

IK02








GLOW
WIRE
850 °C






	LED27S/840 PSU P (W)	LED27S/830 PSU P (W)	LED27S/840 PSD P (W)	LED27S/830 PSD P (W)	LED37S/840 PSU P (W)	LED37S/830 PSU P (W)	LED37S/840 PSD P (W)	LED37S/830 PSD P (W)	kg
RC134B W60L60 OC			22	23	30.5	34.5	35.5	35.5	2.9
RC134B W60L60 NOC	27	28.5	26.5	30.5	34	34	35.5	35.5	2.9
RC134B W30L120 OC			22	23	30.5	34.5	35.5	35.5	3
RC134B W30L120 NOC	27	28.5	26.5	30.5	34	34	35.5	35.5	3
RC135B W62L62 OC			22		30.5	34.5	35.5		3.1
RC135B W62L62 NOC	27		26.5		34		35.5		3.1
RC134B W60L60 ELB3 OC			25.5				39		3.6
RC134B W60L60 ELB3 NOC	30.5				38		39		3.6
RC134B W30L120 ELB3 OC			25.5				39	39	3.75
RC134B W30L120 ELB3 NOC	30.5	32		34	38	38	39	39	3.75









	A	B	C	D
RC134B / RC135B W60L60	41	597	597	11
RC134B / RC135B W30L120	41	1197	297	21
RC134B / RC135B W62L62	41	622	622	11




PCV (Plaster ceiling version)

Module	A(mm)	B(mm)		
RC134Z W60L60	615	615	12-24	200
RC134Z W30L120	315	1215	12-24	200
RC135Z W62L62	640	640	12-24	200

1**2****3****4****5****6****7**

Inrush current



	LED275/840 PSU NOC	LED275/830 PSU NOC	LED275/840 PSD LED275/830 PSD	LED375/840 PSU NOC LED375/830 PSU NOC	LED375/840 PSU OC	LED375/840 PSD LED375/830 PSD
I _{max} (A)	8	14	14.7	5.3	19	22
T _{ref} (μs)	60	250	250	70	280	275
B-10 A	15	20	23	15	15	15
B-13 A	19	26	30	19	19	19
B-16 A	24	33	38	24	24	24
B-20 A	30	41	47	30	30	30
B-25 A	37	51	59	37	37	37
C-10 A	24	34	39	24	24	24
C-13 A	32	44	51	32	32	32
C-16 A	40	56	64	40	40	40
C-20 A	49	68	79	49	49	49
C-25 A	62	85	98	62	62	62

Maintenance instructions

To assure the lighting quality of this unique LED lighting concept there are a few instructions regarding the maintenance of this LED luminaire:

- ☐ Do not touch electronic components!
Electronic components are under high voltage.
Electronic components are ESD sensitive.
- ☐ During installation or when maintaining the luminaire please use static free gloves to avoid marks on the luminaire.
- ☐ To remove dirt and spots use the following:
 - o Dust: only use micro fiber cloths
 - o Fingerprints, etc.: use a cleaner for synthetic materials with antistatic properties.
- ☐ Do not stare into the LED light beam.
- ☐ To avoid scratches and dirt on optical parts remove protective foil after installation.
- ☐ The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.

