

**90%**  
Energy cost  
saving



## Technical application guide

### Philips Classic LEDspot MV GU10

Classic LEDlamps provide a natural lighting effect for basic general lighting applications, while saving money in energy and lamp replacement.

Classic LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. These are compatible with most existing fixtures with GU10 and are designed as a retrofit replacement for halogen or incandescent spots.

**Product benefits:**

- Easy retrofit
- Long lifetime
- Huge energy saving
- Low heat generation

[www.philips.com/led-product-info](http://www.philips.com/led-product-info)



# PHILIPS

## Design highlights



- 90% energy saving compared to standard halogen spots
- Long lifetime of 15,000 hours (B50, L70)
- Operates at 220–240 V AC and its form-factor is designed as a direct retrofit into all GU10 holders
- Highly focused beam for a clearly defined beam spread
- CCT: 2700 K, 3000 K
- Switching cycles at the rate of 30s ON/ 30s OFF = 50,000 cycles
- No UV and Cool Beam (no IR)
- Environmental friendly, without Mercury or any other hazardous substances
- RoHS compliant



## Application notes


- Operating temperature range is between -20 °C and 45 °C ambient
- Only to apply in dry indoor environments and most of open fixtures with GU10 lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights
- For use in fixtures that can structurally support a lamp weighing 0.060 kilogram

## Technical Specifications


Product type	Voltage	Wattage	Comparable Halogen Wattage	Cap Base	Beam Intensity	Beam Angle	Lifetime	Lumen Output	Efficacy	Dimmable	Color rendering index	Color temp.	Ec	KSA EEI label
	V	W	W		cd	°	hours	lm	lm/W			K		kWh/1000h
CLA LEDspotMV D 4.4-35W GU10 827 36D	220-240	4.4	35	GU10	500	36	15,000	250	57	Yes	>80	2700	5	C
CLA LEDspotMV D 5.5-50W GU10 827 36D	220-240	5.5	50	GU10	650	36	15,000	350	64	Yes	>80	2700	6	C
CLA LEDspotMV D 5.5-50W GU10 830 36D	220-240	5.5	50	GU10	680	36	15,000	365	66	Yes	>80	3000	6	C

## Fixture compatibility


Type	C max. Overall Length (mm)	D max. Diameter (mm)	Weight (g)
Classic LEDspot MV GU10	53	50	60



CLA LEDspotMV D 4.4-35W GU10 2700K




CLA LEDspotMV D 5.5-50W GU10 2700K




## Photometric diagrams

CLA LEDspotMV D 4.4-35W GU10 827 36D


1 x 250 lm






## Temperature

Classic LEDspot MV GU10 is designed for operation in all GU10 lighting installations in open fixtures (10 mm free air space is needed around the lamp housing to ensure long-life).



## Lifetime and sustainability

Failure rate curve of Classic LEDspot MV GU10



- Philips Classic LEDspot MV GU10 has a lifetime of 15,000 hours, defined as the number of hours before 50% of the lamps will fall below 70% of their initial lumens.
- Lifetime estimation is based on the application environment condition: at room temperature (25 °C), free air burning, base down burning position in 10 mm free air to simulate an in-luminaire condition and at rated voltage



© 2016 Philips Lighting  
 All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent or other industrial or intellectual property rights.