


Transforming light into an element of design

TRUGROOVE FLAT CORNER DEFINITION LED PoE



DIRECT DEFINITION, FLUSH SILK LENS
CRI >80 4000K, 2000 lm/4ft

Project:

Spec Type:

Catalog No: 39A0PAGL

Qty

Line Notes:



Ordering guide

Product Type	Source	Color Temp *	Lumens *	Optics	Housing	Ceiling / Trim	Run Length	Wiring	Voltage	Driver
39A0	P	A	G	L	S					
TruGroove Flat Corner Definition LED PoE	P LED PoE	A 4000K B 3500K C 3000K	G 2000 lm/4ft	L Flush Silk Lens	S Standard	1 T-Grid	22 2x2	7 1 cct w/ Dimming	N Not applicable (Class 2)	E Standard

* Nominal values within a range. Consult ies file for exact color temp, lumens and up/down distribution

Mounting Hardware

Recessed	Mount Type Consult separate mounting spec sheet for mount type options
----------	---

Integrated Controls Please indicate with check mark.


No Options Available



TRUGROOVE FLAT CORNER
DEFINITION LED PoE

DIRECT DEFINITION, FLUSH SILK LENS

Photometry



Total Output	1968 lm
Efficacy	83.7 lm/W
CCT	4020K
CRI	84
R9	17
Distribution	0% Up / 100% Down
Spacing Criteria (0/90/180°)	1.25/1.24/NA
Meets RP-1-04 recommendations for VDT-Normal spaces	

Values per straight 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

Lumen maintenance of the LEDs has been tested by the manufacturer in accordance with IESNA LM-80-08

Candela Distribution

Vertical Angle	Horizontal Angle					Zonal Lumens
	0	22.5	45	67.5	90	
0	700	700	700	700	700	0
5	696	697	697	698	697	66
15	670	674	669	672	669	189
25	621	624	618	623	621	286
35	555	557	548	553	546	345
45	463	470	463	467	459	358
55	365	367	357	362	352	322
65	245	251	237	249	243	242
75	119	130	120	129	118	131
85	17	25	20	25	22	29
90	0	0	0	0	0	0
95	0	0	0	0	0	0
105	0	0	0	0	0	0
115	0	0	0	0	0	0
125	0	0	0	0	0	0
135	0	0	0	0	0	0
145	0	0	0	0	0	0
155	0	0	0	0	0	0
165	0	0	0	0	0	0
175	0	0	0	0	0	0
180	0	0	0	0	0	0

Coefficients of Utilization (%)

RCR	Ceiling Wall:	80				70				50			
		70	50	30	10	70	50	30	10	50	30	10	10
0		119	119	119	119	116	116	116	111	111	111	111	111
1		109	104	100	96	106	102	98	98	95	92	92	92
2		99	91	84	78	96	89	83	85	80	76	76	76
3		90	80	72	65	88	78	71	75	69	63	63	63
4		83	71	62	55	80	69	61	67	60	54	54	54
5		76	63	54	47	74	62	53	60	52	47	47	47
6		70	57	48	41	68	56	47	54	46	41	41	41
7		65	51	43	37	63	51	42	49	42	36	36	36
8		60	47	38	33	59	46	38	45	38	32	32	32
9		57	43	35	29	55	42	35	41	34	29	29	29
10		53	40	32	27	52	39	32	38	31	26	26	26

Avg. Luminance (cd/m2)

Vertical Angle	Horizontal Angle		
	0	45	90
55	7280	7112	7027
65	6633	6411	6571
75	5257	5308	5225
85	2291	2618	2836

Electrical Specifications

Input Voltage	PoE (51-54VDC)
Input Power	23.5W
Tested values – contact technical support for rated values. Standby power <0.9W for 4ft <1.8W for 8ft and <2.7W for 6ft	

Modules & Runs


TruGroove LED Corners nominal sizes

2ft x 2ft 90° flat lit corner unit
Inside 90° joiner bracket

*Note: In closed pattern applications, sensor is located remote from pattern.
In open pattern applications, sensor is located at one end of the pattern.*

Refer to module size details below for actual dimensions. T-grid corner units are 2' on-center, so extend past the T-bar when combined with standard 4' & 8' modules.
Please provide pattern drawings or sketches with dimensions based on lens centerlines.
To specify continuous straight runs, refer to TruGroove Continuous data sheets.


Flat Patterns – with flat corners; 2'x2' corners and straight sections in 4' increments only.



Module Dimensions

Flat 90° Lit Corner Units


T-Grid



Nominal length	Housing	Lens aperture	Trim – T-Grid
2 x 2ft Flat	25.7"/653 mm	N / A	25.9"/658 mm

Options and Details

T-grid*



* Compatible with TechZone™ 4" Ceiling Grid

Trim Views

Flush lens



T-grid

Housing

Die-formed 20 gauge cold-rolled steel. Multiple upper wire entrances available for continuous row mounting of fixtures.

Weight

Maximum 3.5lb/ft.

Optical System

Performance version: White light emitted from the LED sources is internally reflected and laterally redirected by a biconvex lens. Light is then reflected by Miro Silver panels and exits through the optical lens assembly. This assembly contains acrylic extrusion profiles to retain a layer of MesoOptics film, creating both an uninterrupted continuum of light and an optical batwing distribution.

Definition version: Light passes through a diffuse white acrylic lens to deliver a highly uniform luminous continuum.

Driver

Philips PoE Lighting Controller.

Lumen Maintenance

At an ambient temperature of 25°C in non-insulated contact applications, the LED lumen maintenance expectation for each lumen package is:

G: L₉₀ (12k) 68,000 hrs

Mounting

Mounting brackets on housing sides support T-Grid installation.

Joints

Self-aligning joining system with hands-free pre-joining wire access.

Electrical

Wire Access Cover provides RJ45 connection point for PoE network.

Approvals

Certified to UL, CSA and IES standards. Insulation Contact (IC) rated.

Finish

Extruded aluminum trim and die-cast endplates coated with electrostatically applied and thermally cured polyester powder coat paint finish.

Environment

Rated for dry or damp locations in operating ambient temperatures 0-40°C (32-104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants are not covered under warranty.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.



© 2014 Koninklijke Philips N.V. All rights reserved.
Specifications are subject to change without notice.
www.philips.com/linaires

TruGrvCnrFlatDefnP_40K20lm_L.pdf 07.15 page 4 of 4

Philips Lighting
North America Corporation
200 Franklin Square Drive
Somerset, NJ 08873
Phone: 855-486-2216