

Transforming light into an element of design

DIRECT PERFORMANCE, FLUSH MESOOPTICS LENS
CRI >80 4000K, 2000 lm/4ft

Project:

Spec Type:

Catalog No: 39S1PAGQ

Qty

Line Notes:

TRUGROOVE STANDALONE PERFORMANCE LED PoE



Ordering guide

Product Type	Source	Color Temp *	Lumens *	Optics	Housing	Ceiling / Trim	Run Length	Wiring	Voltage	Driver
39S1	P	A	G	Q	S					
TruGroove Standalone Performance LED PoE	P LED PoE	A 4000K B 3500K C 3000K	G 2000 lm/4ft	Q Flush Meso Lens	S Standard	1 T-Grid	XX Total run length (4' increments)	7 1 cct w/ Dimming	N Not applicable (Class 2)	E Standard

* Nominal values within a range. Consult ies file for exact color temp, lumens and up/down distribution

Mounting Hardware

<input type="checkbox"/> Recessed	Mount Type Consult separate mounting spec sheet for mount type options
-----------------------------------	---


Integrated Controls Please indicate with check mark.

☐ Philips Actilume Daylight and Occupancy Sensor (DO)



DIRECT PERFORMANCE, FLUSH MESOOPTICS LENS

Photometry



Total Output	1994 lm
Efficacy	87.5 lm/W
CCT	4020K
CRI	84
R9	17
Distribution	0% Up / 100% Down
Spacing Criteria (0/90/180°)	1.36/1.56/NA
Meets RP-1-04 recommendations for VDT-Intensive spaces	

Values per 4ft unit

Fixture photometry has been conducted in accordance with IESNA LM-79-08

Lumen maintenance of the LEDs has been tested by the manufacturer in accordance with IESNA LM-80-08

Candela Distribution

Vertical Angle	Horizontal Angle					Zonal Lumens
	0	22.5	45	67.5	90	
0	706	706	706	706	706	0
5	704	707	715	717	725	69
15	695	715	761	794	819	216
25	680	728	819	892	925	373
35	616	667	737	807	820	450
45	431	451	462	505	478	366
55	274	285	281	294	286	257
65	165	172	166	173	164	168
75	77	79	72	75	69	80
85	10	13	11	12	10	15
90	0	0	0	0	0	0
95	0	0	0	0	0	0
105	0	0	0	0	0	0
115	0	0	0	0	0	0
125	0	0	0	0	0	0
135	0	0	0	0	0	0
145	0	0	0	0	0	0
155	0	0	0	0	0	0
165	0	0	0	0	0	0
175	0	0	0	0	0	0
180	0	0	0	0	0	0

Coefficients of Utilization (%)

RCR	Ceiling Wall:	80				70				50			
		70	50	30	10	70	50	30	10	50	30	10	10
0		119	119	119	119	116	116	116	111	111	111	111	111
1		110	106	102	99	108	104	100	100	97	94	94	94
2		101	94	88	83	99	92	87	89	84	80	80	80
3		93	84	76	70	91	82	75	79	73	69	69	69
4		86	75	67	61	84	74	66	71	65	59	59	59
5		79	67	59	53	77	66	58	64	57	52	52	52
6		74	61	53	47	72	60	52	58	51	46	46	46
7		68	56	47	41	67	55	47	53	46	41	41	41
8		64	51	43	37	62	50	42	49	42	37	37	37
9		60	47	39	34	58	46	39	45	38	33	33	33
10		56	43	36	30	55	43	35	42	35	30	30	30

Avg. Luminance (cd/m2)

Vertical Angle	Horizontal Angle		
	0	45	90
55	5459	5599	5701
65	4458	4486	4450
75	3390	3169	3060
85	1285	1379	1258

Electrical Specifications

Input Voltage	PoE (51-54VDC)
Input Power	22.8W
Tested values – contact technical support for rated values. Standby power <0.9W for 4ft <1.8W for 8ft and <2.7W for 6ft	

Modules & Runs

TruGroove Standalone LED nominal housing lengths
4ft & 8ft


Standalone Modules
T-Grid



Refer to module size details below for actual dimensions e.g. trim. T-grid units fit within a standard 2' grid.
To specify continuous runs, refer to TruGroove Continuous data sheets.

Module Dimensions


Standalone recessed
T-Grid



Nominal length	Housing	Lens aperture	Mounting points	Trim – T-Grid
4ft	47.9"/1217 mm	47.0"/1194 mm	47.4"/1204 mm	47.75"/1213 mm
8ft	95.9"/2436 mm	95.0"/2413 mm	95.4"/2423 mm	95.75"/2432 mm

Options and Details


T-grid*



* Compatible with TechZone® 4" Ceiling Grid and Armstrong Formations

Trim Views

Flush lens



T-grid

Housing

Die-formed 20 gauge cold-rolled steel. Multiple upper wire entrances available for continuous row mounting of fixtures.

Weight

Maximum 3.5lb/ft.

Optical System

Performance version: White light emitted from the LED sources is internally reflected and laterally redirected by a biconvex lens. Light is then reflected by Miro Silver panels and exits through the optical lens assembly. This assembly contains acrylic extrusion profiles to retain a layer of MesoOptics film, creating both an uninterrupted continuum of light and an optical batwing distribution.

Definition version: Light passes through a diffuse white acrylic lens to deliver a highly uniform luminous continuum.

Driver

Philips PoE Lighting Controller.

Lumen Maintenance

At an ambient temperature of 25°C in non-insulated contact applications, the LED lumen maintenance expectation for each lumen package is:

G: L₉₀ (12k) 68,000 hrs

Mounting

Mounting brackets on housing sides support T-Grid installation.

Joints

Self-aligning joining system with hands-free pre-joining wire access.

Electrical

Wire Access Cover provides RJ45 connection point for PoE network.

Approvals

Certified to UL, CSA and IES standards. Insulation Contact (IC) rated.

Finish

Extruded aluminum trim and die-cast endplates coated with electrostatically applied and thermally cured polyester powder coat paint finish.

Environment

Rated for dry or damp locations in operating ambient temperatures 0-40°C (32-104°F). Certain luminaire components may be adversely affected by contaminants. Damage caused by sulfur, chlorine, petroleum based solutions or other contaminants are not covered under warranty.

Due to continuing product improvements, Philips Ledalite reserves the right to change the specifications without notice.



© 2014 Koninklijke Philips N.V. All rights reserved.
Specifications are subject to change without notice.
www.philips.com/linaires

TruGrvStndPerfmP_40K20lm_Q.pdf 07.15 page 4 of 4

Philips Lighting
North America Corporation
200 Franklin Square Drive
Somerset, NJ 08873
Phone: 855-486-2216