

# PHILIPS LIGHTOLIER

## Downlighting

### Calculite LED gen 3 4" square tunable white

1000 & 1200lm



Project: \_\_\_\_\_  
Location: \_\_\_\_\_  
Cat.No: \_\_\_\_\_  
Type: \_\_\_\_\_  
Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
Notes: \_\_\_\_\_

Calculite LED 4" generation 3 features industry leading visual comfort, excellent uniform illumination over time, and patented installation flexibility.

Complete product = Frame + Engine + Trim

#### Frame

example: C4SN

Series	Aperture	Installation	Voltage/Options
<b>C4</b>	<b>S</b>		
<b>C4</b> Calculite LED 4" aperture	<b>S</b> Square	<b>N</b> New Construction <b>R</b> Remodeler	— Universal (120/277V) <b>3</b> 347V <b>EM</b> Emergency <sup>1,2</sup> <b>LC</b> Chicago Plenum <sup>1</sup>
		<b>A</b> Airseal IC	— Universal (120/277V)

#### Engine

example: C4L10865MDUTW

Series	Lumens	CRI	CCT	Beam	Dimming	Voltage	Options
<b>C4L</b>							<b>TW</b>
<b>C4L</b> Calculite LED 4" aperture	<b>10</b> 1000lm	<b>8</b> 80 CRI	<b>65</b> 6500-2700K	<b>M</b> Medium (56°) <sup>4</sup> <b>W</b> Wide (76°)	<b>D</b> Dali	<b>U</b> Universal (120/277V/347V)	<b>TW</b> Tunable White
	<b>12</b> 1200lm <sup>3</sup>						

#### Trim

example: C4SDLNMCCP

Series	Aperture	Style	Beam <sup>3</sup>	Finish	Flange
<b>C4</b>	<b>S</b>				
<b>C4</b> Calculite LED 4" aperture	<b>S</b> Square	<b>DL</b> Downlight	<b>NM</b> Narrow & Medium <sup>4</sup> <b>W</b> Wide	<b>CL</b> Specular clear <b>CC</b> Comfort clear <b>CD</b> Comfort clear diffuse	— White (matte) <b>P</b> Polished <b>F</b> Flangeless
		<b>LW</b> Lensed Wall Wash <sup>4</sup>	— blank	<b>WH</b> White (matte)	— White (matte) <b>F</b> Flangeless

#### Mixing chambers

	6" Med	6" Wide
<b>4" cone</b>	0.8 s.c. (52°)	1.1 s.c. (72°)

#### Accessories (ordered with a flangeless trim)


**CA4SFT** Mud-in ring for use with flangeless installations.

- Emergency (EM) and Chicago Plenum (LC) options are only available with New construction (N) installations.
- Emergency (EM) frame comes with emergency battery pack and ceiling mountable test switch. Reflector mounted test switch requires above ceiling access and is only available with the downlight option. For reflector mounted test switch, order emergency frame and add "EM" suffix to reflector (example: C4SDLNMCCEM).
- The 1200lm is only compatible with Airseal (C4RA or C4SA) frame.
- Medium (M) beam is ideal for lensed wall washing.


# C4STW Calculite LED generation 3

4" square tunable white


## New Construction (N)




## Chicago Plenum (LC)



## Remodeler (R)



## Flangeless mud-in ring (CA4SFT)



Consult factory for wood installation instructions.

## Beam options

	4" Med engine	4" wide engine
4" reflector	52° (0.8 s.c.)	72° (1.1 s.c.)

## Lifetime (TM-21) data

Lumens	Narrow beam	Medium/Wide beam*
500lm		
1000lm	L90 @ 60,000hrs.	L90 @ 60,000hrs.
1500lm		
2000lm		
2500lm	L90 @ 60,000hrs.	L85 @ 60,000hrs.
3000lm*		

\* Lutron 3000lm with Medium/Wide beam is L80 @ 60,000hrs.

# C4STW Calculite LED generation 3

## 4" square tunable white

### Frame-in-kits

#### New Construction

Galvanized stamped steel for dry or plaster ceilings. Preinstalled telescoping mounting bars from 13" to 24". For 4' distances, use 1/2" EMT, 1-1/2" x 1/2" U or C channel.

**Max ceiling thickness is 2".**

#### AirSeal

Black painted steel housing for dry or plaster ceilings. Pre-installed telescoping mounting bars from 13" to 24".

#### Patented install Mounting frame

With no driver attached, this versatile frame is independent of driver accommodating a wide range of lumen packages, driver types and CCTs, including 120V and 277V inputs.

Close-cut aperture design eliminates the possibility of undesired gap between ceiling opening and reflector flange.

Separate wiring compartment for wiring frame to building allows inspection prior to light engine installation.

Simple plug-and-play connection between the frame and light engine from below the ceiling eliminates the need for wiring between frame and LED driver, and also saves time during installation and future replacements/upgrades. Plug-and-play receptacle accommodates technology upgrade of light engines and replacements for the life of the building.

### Optical systems

#### Comfort throughout the space

Patented optical system combines primary and secondary optics to provide a true 50° physical cutoff and 45° reflected cutoff virtually eliminating the view of the light source and bright spots in the reflector.

A new reflector curve reduces reflector brightness by up to 50% compared to existing products, allowing for the use of higher lumen packages in smaller apertures without creating bright spots in the ceiling.

#### Quality of light

2 SDCM ensures color consistency from fixture to fixture and over the luminaire's long lifetime.

Proprietary optical grade silicone lens with patterned surface provides soft, even beam diffusion without hotspots or dark rings.

### Light Engine

Quick connect power pack comprised of light source and driver allow for easy installation and replacement from below ceiling with no need for additional wiring. This allows for

- Frame and ceiling installation to be performed while still finalizing details such as lumen packages, CCT and control type.
- Easy replacement of electronics at end of life with minimal wasted material and labor required.
- Ease and upgradability of technology.

### Drivers

- EldoLED ECOdrive Dali 1% Dimming

### Options and Accessories

**Flangeless mud-in ring:** Use **CA4SFT** for use with flangeless installations.

### Labels and Listings

cULus listed for wet locations

IBEW Union made (light engines & reflectors)

RoHS compliant


### Warranty

5 year warranty on complete system.

Complete warranty available at: [http://images.philips.com/is/content/PhilipsConsumer/PDFDownloads/United%20States/ODL20150930\\_003-UPD-en\\_US-Philips-warranty-indoor-PLS-us.pdf](http://images.philips.com/is/content/PhilipsConsumer/PDFDownloads/United%20States/ODL20150930_003-UPD-en_US-Philips-warranty-indoor-PLS-us.pdf)

### Color information

4" 1000lm	2700K	3000K	3500K	4000K	5000K	6500K
Flux (lms)	909	920	942	951	927	927
Power (W)	10.24	10.24	10.22	10.19	9.94	9.98
Efficacy (lm/W)	88.8	89.8	92.2	93.4	93.3	92.8
CCT	2766	2974	3423	3933	4866	6458
CRI	86	87	88	89	87	83
R9	21	26	33	36	32	13
x	0.4513	0.4335	0.404	0.3797	0.3483	0.3136
y	0.4034	0.394	0.3783	0.3653	0.3483	0.3288
Duv	-0.0019	-0.0036	-0.0053	-0.0052	-0.0029	0.0026




# C4STW Calculite LED generation 3

4" square tunable white

## Medium beam, 1500lm Engine, 103.8 lm/w

Candela Curve



Frame: **C4SN**  
 Engine: **C4L15835MZ10U**  
 Trim: **C4SDLNMCL**  
 CCT<sup>1</sup>: 3500K  
 Output lumens: 1475 lms  
 Input watts: 14.2 W (±5%)  
 CRI: 80 min  
 Spacing Crit.: 0.9  
 Beam Angle: 58°

Zonal summary

Zone	Lumens	%Luminaire
0-30	1092	74.0%
0-40	1393	94.5%
0-60	1475	100.0%
0-90	1475	100.0%

Angle	0°	45°	Lms
0	1414	1414	139
5	1442	1442	
10	1481	1484	
15	1494	1522	422
20	1387	1485	
25	1119	1287	531
30	755	943	
35	430	561	301
40	217	285	
45	100	129	82
50	0	0	0
55	0	0	0
60	0	0	0
65	0	0	0
70	0	0	0
75	0	0	0
80	0	0	0
85	0	0	0
90	0	0	0

Single unit data

Height to lighted plane	Initial center beam foot-candles	Beam diameter (ft)*
5'	57	4.5'
6'	39	5.4'
7'	29	6.3'
8'	22	7.2'
9'	17	8.1'

\* Beam diameter is where foot-candles drop to 50% of maximum.

Multiple unit data - RCR 2

Spacing on center	Initial center beam foot-candles	Watts per sq. ft.
5'	67.5	0.63
6'	44.3	0.41
7'	31.6	0.30
8'	26.4	0.25
9'	21.1	0.20

38' x 38' x 10' Room, Workplane 2.5' above floor, 80/50/20% Reflectances

**Efficacy: 103.8 lm/w**  
 Report#: T20161398

Adjustment factors


Finish	CCT	Lumens
CL = 100%	80CRI 4000K = 102%	3000lm = 200%
CC = 95%	80CRI 3500K = 100%	2500lm = 167%
CD = 87%	80CRI 3000K = 97%	2000lm = 133%
CZ = 63%	80CRI 2700K = 87%	1500lm = 100%
WH = 87%	90CRI 3000K = 77%	1000lm = 67%
BK = 57%	90CRI 2700K = 73%	500lm = 33%

Coefficients of utilization

Celling	80%				70%				50%				30%				0%
Wall	70	50	30	10	50	10	50	10	50	10	50	10	50	10	50	10	0
RCR	Zonal cavity method - Effective floor reflectance = 20%																
Room Cavity Ratio	0	119	119	119	119	116	116	111	111	106	106	100	100	106	106	100	100
1	114	111	109	106	109	105	105	101	101	98	98	94	94	96	96	91	87
2	108	103	99	96	102	95	95	93	93	86	86	82	82	80	80	73	71
3	103	97	92	88	95	87	87	86	86	80	80	76	76	74	74	68	66
4	98	90	85	81	89	80	80	79	79	76	76	72	72	70	70	64	62
5	93	85	79	75	84	74	74	73	73	69	69	66	66	64	64	60	58
6	88	79	74	69	79	69	69	68	68	64	64	61	61	59	59	55	53
7	84	75	69	65	74	64	64	63	63	60	60	57	57	55	55	51	49
8	80	70	64	60	70	60	60	59	59	56	56	53	53	51	51	47	45
9	76	66	61	57	66	57	57	56	56	53	53	50	50	48	48	44	42
10	72	63	57	53	62	53	53	52	52	50	50	47	47	45	45	41	39

## Wide beam, 1500lm Engine, 90.8 lm/w

Candela Curve



Frame: **C4SN**  
 Engine: **C4L15835MZ10U**  
 Trim: **C4SDLWCL**  
 CCT<sup>1</sup>: 3500K  
 Output lumens: 1288 lms  
 Input watts: 14.2 W (±5%)  
 CRI: 80 min  
 Spacing Crit.: 1.2  
 Beam Angle: 69°

Zonal summary

Zone	Lumens	%Luminaire
0-30	725	56.3%
0-40	1141	88.6%
0-60	1288	100.0%
0-90	1288	100.0%

Angle	0°	45°	Lms
0	688	688	69
5	713	709	
10	766	757	
15	846	837	237
20	907	904	
25	923	928	419
30	854	878	
35	666	720	416
40	410	466	
45	163	181	146
50	28	27	0
55	0	0	1
60	0	0	0
65	0	0	0
70	0	0	0
75	0	0	0
80	0	0	0
85	0	0	0
90	0	0	0

Single unit data

Height to lighted plane	Initial center beam foot-candles	Beam diameter (ft)*
5'	28	6.0'
6'	19	7.2'
7'	14	8.4'
8'	11	9.6'
9'	8	10.8'

\* Beam diameter is where foot-candles drop to 50% of maximum.

Multiple unit data - RCR 2

Spacing on center	Initial center beam foot-candles	Watts per sq. ft.
5'	57.9	0.63
6'	38.0	0.41
7'	27.1	0.29
8'	22.6	0.25
9'	18.1	0.20

38' x 38' x 10' Room, Workplane 2.5' above floor, 80/50/20% Reflectances

**Efficacy: 90.8 lm/w**  
 Report#: T20161399

Adjustment factors

Finish	CCT	Lumens
CL = 100%	80CRI 4000K = 102%	3000lm = 200%
CC = 95%	80CRI 3500K = 100%	2500lm = 167%
CD = 87%	80CRI 3000K = 97%	2000lm = 133%
CZ = 63%	80CRI 2700K = 87%	1500lm = 100%
WH = 87%	90CRI 3000K = 77%	1000lm = 67%
BK = 57%	90CRI 2700K = 73%	500lm = 33%

Coefficients of utilization

Celling	80%				70%				50%				30%				0%
Wall	70	50	30	10	50	10	50	10	50	10	50	10	50	10	50	10	0
RCR	Zonal cavity method - Effective floor reflectance = 20%																
Room Cavity Ratio	0	119	119	119	119	116	116	111	111	106	106	100	100	106	106	100	100
1	113	110	107	105	108	103	103	104	100	98	98	94	94	96	96	91	87
2	107	102	97	93	100	92	92	97	90	86	86	82	82	80	80	73	71
3	101	94	88	84	92	83	83	90	82	78	78	74	74	71	71	67	65
4	95	87	80	76	85	75	75	83	74	70	70	67	67	64	64	60	58
5	89	80	74	69	79	69	69	77	68	64	64	61	61	59	59	55	53
6	84	74	67	63	73	63	63	72	62	59	59	56	56	53	53	50	48
7	79	69	62	57	68	57	57	67	57	54	54	51	51	49	49	45	43
8	74	64	57	53	63	53	53	62	52	50	50	47	47	45	45	41	39
9	70	59	53	49	59	48	48	58	48	46	46	43	43	41	41	37	35
10	66	56	49	45	55	45	45	54	45	43	43	40	40	38	38	34	32

1. Correlated Color Temperature within specs as defined in ANSI, NEMA, ANSLG C78.377-2008: Specifications for the Chromaticity of Solid State Lighting Products.
2. Tested using absolute photometry as specified in LM79: IESNA Approved Method for the Electrical and Photometric Measurements of Solid-State Lighting Products.

© 2017 Philips Lighting Holding B.V. All rights reserved.  
 Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.  
[philips.com/luminaires](http://philips.com/luminaires)



Philips Lighting, North America Corporation  
 200 Franklin Square Drive, Somerset, NJ 08873  
 Tel. 855-486-2216

Philips Lighting Canada Ltd.  
 281 Hillmount Rd, Markham, ON, Canada L6C 2S3  
 Tel. 800-668-9008