

HADCO


by @signify

Urban

Stockholm

53630 Post top

Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____



Ordering Guide

Example: 53630 ABS A D 50H E B N

Product Code	53630	Stockholm
Finish	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN RBZ SRT VBZ VCP VGN VTC WBZ WHT	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White
Panel/Globe	A	Clear Acrylic
Socket	D G L	Medium Mogul LED
Wattage/Source	50H 70H 35S 50S 70S 100S 100I LED	50W MH 70W MH 35W HPS 50W HPS 70W HPS 100W HPS 100W INC. LED
Voltage	E F G H	120V 208V 240V 277V
Distribution	B C P N	6" Type V Distrib. 6" Type III Distrib. Type V - Cutoff *1 Optics None
Photoeye	N	None

*1 Medium socket only.

53630 Stockholm

Post top

Specifications

CONSTRUCTION:

Cast aluminum finial. Spun aluminum cap. Spun aluminum roof. Fluted cast aluminum top ring. 4 Cast aluminum legs. Cast aluminum refractor support. Fitter slips over 3" O.D. post or tenon.

FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

PANELS/LENS/GLOBE:

See lenses for available options.

LAMPING:

Lamp is not included.

ELECTRICAL ASSEMBLY:

Lantern will be prewired and tested. All electrical components are ETL listed.

BALLAST:

Ballast and component parts mounted inside two-piece cast aluminum moisture proof ballast compartment. (Customer must specify wattage and voltage.)

MOUNTING:

Fixture mounts to 3" dia. post or tenon.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL Listed to U.S. safety standards for wet locations. cETL Listed to Canadian safety standards for wet locations.

Height:

36 3/4"

Width:

17 3/4"

Fitter:

3" I.D.

EPA:

1.96

Max. Weight:

28 lbs.

