

PHILIPS

Bulb

LED

9W-65W

E26

Daylight

046677541026



Bright LED lighting with excellent light quality

Philips LED light bulbs provide a cool white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your matted traditional bulbs.

Choose for a sustainable solution

- Saves up to 80% Energy

Light beyond illumination

- A simple LED for everyday use
- Instant on

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Instant on Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: E26
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 13 cm
- Weight: 0.075 kg
- Width: 9.5 cm

Durability

- Average life (at 2.7 hrs/day): 11 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 11,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 110 degree(s)
- Color consistency: ANSI
- Color rendering index (CRI): 80
- Color temperature: 5000 K
- Light Color Category: Daylight
- Nominal luminous flux: 650 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 125 mA
- Efficacy: 72 lm/W

Packaging information

- EAN: 046677541026
- EOC: 541029
- Product title: 9BR30/LED/850/FR/P/ND 6/1FB

Power consumption

- Power factor: >0.5
- Voltage: 120 V
- Wattage: 9 W
- Wattage equivalent: 65 W

Product dimensions & weight

- Length: 13 cm

Rated values

- Rated beam angle: 110 degree(s)
- Rated lifetime: 11,000 hour(s)
- Rated luminous flux: 650 lumen
- Rated power: 9 W

Technical specifications

- Frequency: 60 Hz

Bulb characteristics

- EAN/UPC - product: 046677541026
- Rated beam angle: 110 degree(s)
- Height: 13 cm
- Average life (at 2.7 hrs/day): 11 year(s)
- Beam angle: 110 degree(s)
- Lamp current: 125 mA
- Net weight: 0.095 kg
- Rated lifetime: 11,000 hour(s)
- Intended use: Indoor
- Weight: 0.075 kg
- Lumen maintenance factor: 70%
- Color consistency: ANSI
- Gross weight: 0.115 kg
- EAN: 046677541026
- Rated luminous flux: 650 lumen
- Lamp shape: Non directional reflector
- Width: 9.5 cm
- Color rendering index (CRI): 80
- Height: 13.100 cm
- EOC: 541029
- Socket: E26
- Number of switch cycles: 50,000
- Color temperature: 5000 K
- EyeComfort: Yes
- Length: 9.100 cm
- Product title:
9BR30/LED/850/FR/P/ND 6/1FB
- Power factor: >0.5
- Rated power: 9 W
- Technology: LED
- Light Color Category: Daylight
- Width: 9.100 cm
- Voltage: 120 V
- Type of glass: Frosted
- Nominal luminous flux: 650 lumen
- Material number (12NC):
929001948003
- Wattage: 9 W
- Length: 13 cm
- Starting time: 0.5 s
- Wattage equivalent: 65 W
- Warm-up time to 60% light: Instant full light
- Frequency: 60 Hz



Issue date: 2022-06-12
Version: 0.15

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com