



Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Ordering Guide

Example: I4 G H

<b>Product Code</b>	I4	Incandescent	
<b>Rock Guard</b>	G	Rock Guard	*1
<b>Finish</b>	H	Bronze	
	SS	Stainless steel (MATTE FINISH)	
	N	Natural Bronze	

\*1 Rock guard is optional and available in bronze and natural brass only.

### Specifications

#### HOUSING:

Single-piece compression molded fiberglass reinforced polyester composite, factory pressure tested to ensure water will not wick or leak through. Trim ring is a compression molded polyester. Rock guard used for directional glare control made of compression molded polyester. Single-piece molded silicone U-channel gasket.

#### FINISH:

Composite is textured, pressure formed, molded-in-color.

#### OPTICAL ASSEMBLY:

2,600-pound live-load rated, standard walk-over lens. Clear convex, tempered soda-lime glass for high impact resistance. Lamps have 15° articulation either side of vertical and 358° rotation without interruption of beam pattern.

#### LAMPING:

150W maximum PAR38/R40 incandescent lamp. Lamp is not included. Lower wattage lamps are acceptable.

#### ELECTRICAL ASSEMBLY:

4kv rated porcelain mini-can base. Nickel-plated screw shell with center contact.

#### WARRANTY:

Ten-year limited warranty.

#### CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards. ADA Compliant when used in concrete and flush mounted with CP4 or CPS4.

#### IP RATING:

IP67 Dust tight and sealed against direct jets of water and against prolonged effects of immersion.

**Height :** 14" (354mm)  
**Width:** 12 1/4" (310mm)  
**Max. Weight:** 14.06 lb.

