


## Installation

- 1. Connect the red wire to live, Black wire to Neutral and the Green-yellow wire to ground. After joining Properly insulate the wires using good quality Electrical insulation tape.
- 2. Unfasten the Check nuts and loosen the mounting screws to the required height as per the pole size.(Fig 1)
- 3. Insert the pole up to the position shown in the drawing below (Fig 2)
- 4. Tighten both the mounting screws with tightening torque of 4Nm and then tighten the Check nuts fully (Fig 3).




**Philips Lighting India Limited** 

Philips Lighting

## **Installation Instruction**

BRP 042

Street Lighting Luminaire



Type : BRP042 Light Source : LED's

Voltage : 240 V, 50 Hz

IP Classification : IP-65
Net Weight : 0.8 kg
Max. Projected Area : .03 m²

Application : Outdoor use only

Mounting position : Horizontal Application height : Upto 6m Pole Outer Diameter : 32-40mm



## **CAUTION**

- Ensure Earthing is connected.
   Ensure 3 core CABLE for Connections(diameter 5-7mm)
   Cable Entry gland should be properly tightened.
   Product should be operated between 100-300V a.c.
   Use Surge protection (upto 10kV) to protect against surges
   Use Type B+C surge type SPD in distribution box to arrest switching and lighting surges.

FAILURE OF PRODUCT DUE TO NON COMPLIANCE TO ANY OF THE ABOVE, VOIDS WARRANTY OF PRODUCT