

**PHILIPS**  
**HADCO**



Urban

Hagerstown

TX03 Post top luminaire



# Adorn **your space**

Philips Hadco's Hagerstown LED post top gives you the ability to create a unique style through our modular post top concepts to blend into any residential and historic urban settings. With the latest LED technology you can seamlessly replace traditional HID technology to maximize energy savings and significantly reduce total cost of ownership. The Hagerstown luminaire provides excellent uniformity, traditional customizable look, with the benefits of modern technology.



# Hagerstown

## Benefits

- Offers design flexibility with a variety of pods, finials and finishes
- Multiple distribution options and lumen packages suitable for several applications
- The Optical Rib globe disperses light for more uniform coverage while virtually reducing glare
- IP66 rated optical chamber and LED driver ensure lasting durability and reliability
- Dimming controls available for additional energy savings during off-peak hours



**Lumen range:** 3273-14931  
**Wattage range:** 35-137  
**Efficacy range:** 86-122

1. Low-copper spun aluminum roof
2. Optical Rib Technology globe
3. 120-277 or 347-480 VAC driver, 350 mA, 50/60 Hz auto-sensing
4. 10kV/10kA surge suppression, <3kV built into drivers
5. Programmable 0 - 10V dimming

Shown to the left with Pod (B) and Finial (A) TX0348G2BA2A5EWA5DDASTCLONSP1H



Weight: 37 lbs.  
 EPA: 1.7 sq.ft.

## Ordering guide

Series	LEDs	Gen.	Pods	Finials	Fasteners	Finishes	Optics	Photo controls
<b>TX03</b>	<input type="checkbox"/>	<b>G2</b>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
<b>TX03</b> Hagerstown LED post top	<b>32</b> 32 <b>48</b> 48 <b>64</b> 64	<b>G2</b> Gen2	<b>A</b> Octagonal style <b>B</b> Round fitter with scalloped petals <b>C</b> Fluted tapered hourglass <b>D</b> Smooth tapered hourglass <b>E</b> Tapered fluted with scalloped petals <b>G</b> Tall round fluted <b>H</b> Round contemporary <b>J</b> Tapered fluted with round stepped fitter <b>L</b> Round fluted long <b>T</b> Decorative leaf with scalloped petals	<b>A</b> A finial <b>B</b> B finial <b>C</b> C finial <b>D</b> D finial <b>E</b> E finial <b>F</b> F finial <b>G</b> G finial <b>H</b> H finial <b>N</b> No finial	<b>1</b> Hex head bolts <b>2</b> Allen head bolts	<b>A</b> Black <b>B</b> White <b>G</b> Verde <b>H</b> Bronze <b>J</b> Green	<b>3</b> Type 3 <b>5</b> Type 5 <b>3W</b> Type 3 Wide	<b>Button eye photo controls</b> <b>E</b> 120 VAC <b>H</b> 208/240/277 VAC <b>K</b> 347 VAC  <b>R</b> Twist-lock receptacle  <b>N</b> No photo control

Ordering guide continued				Optional programs				
Color Temps	Voltages	Currents	Optional dimming	1st option	2nd option	3rd option	Surge protection	Options
<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>
<b>W</b> 3000K <b>N</b> 4000K	<b>A</b> 120-277 VAC <b>B</b> 347-480 VAC	<b>3</b> 350mA <b>5</b> 530 mA <b>7</b> 700mA <b>1</b> 1050mA	<b>DA</b> 4hrs 25% reduction <b>DB</b> 4hrs 50% reduction <b>DC</b> 4hrs 75% reduction <b>DD</b> 6hrs 25% reduction <b>DE</b> 6hrs 50% reduction <b>DF</b> 6hrs 75% reduction <b>DG</b> 8hrs 25% reduction <b>DH</b> 8hrs 50% reduction <b>DJ</b> 8hrs 75% reduction <b>DALI</b> Compatible with DALI <b>N</b> No dimming	<b>AST</b> Adjustable Start Up <b>N</b> No 1st option	<b>CLO</b> Constant Light Output <b>N</b> No 2nd option	<b>OTL</b> Over The Life <b>N</b> No 3rd option	<b>SP1</b> 10kV/10kA (standard) <b>SP2</b> 20kV/20kA (optional)	<b>H</b> HSS <b>N</b> No options

Prior to ordering, consult specification sheets please visit [www.philips.com/luminaires](http://www.philips.com/luminaires) for the most current information, notes, and exclusions.

© 2016 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting, North America Corporation  
 200 Franklin Square Drive, Somerset, NJ 08873  
 Tel. 855-486-2216

Philips Lighting Canada Ltd.  
 281 Hillmount Rd, Markham, ON, Canada L6C 2S3  
 Tel. 800-668-9008