

HADCO


by @signify

Landscape

Floodlyte

WBM1 Aluminum

Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____



Ordering Guide

Example: WBM1 F A

Product Code	WBM1	Aluminum Floodlyte
Lens	F	Frosted Lens *1
Finish	A B H G	Black White Bronze Verde

*1 Frosted lens is optional.

Specifications

HOUSING:

Die-cast aluminum. Gasketing is silicone. Fully-adjustable swivel arm with vibration-proof locking teeth. Fasteners are 300 series stainless steel. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

OPTICAL ASSEMBLY:

Clear tempered glass lens. Frosted tempered glass lens.

LAMPING:

75W maximum T3 mini candelabra lamp. Lamp is not included. Lower wattage lamps are acceptable.

ELECTRICAL ASSEMBLY:

Mini-candelabra socket (E11). Fixture is pre-wired with 18 AWG black, white, and ground wires.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Height :

4 7/8" (123mm)

Width:

6 7/8" (175mm)

Length:

3 7/16" (88mm)

Max. Weight:

1.7 lb

@signify