LUMEC

by signify

Tunnels demand reliable solutions



Roadway


TunnelView & TubeLi<u>ne</u>





Tunnel and underpass lighting is a complex and demanding field...

So we know you can't afford to compromise.



In the tunnel business for over 20 years, Lumec is now offering a broad range of new LED solutions and controls. With the Lumec brand, you can have total confidence for all your tunnel and underpass needs.

Correct tunnel and underpass lighting is vital for users' safety to prevent sudden changes in light intensity that adversely affect vision. Also paramount to you, is finding installer-friendly solutions which can lower maintenance costs and are worry-free, while providing quality, efficient, and reliable illumination.

You can satisfy all of these demands with **Lumec TunnelView** and **TubeLine** LED luminaires. Whether you want to upgrade your linear tunnel lighting or need one for one replacement of existing traditional point source luminaires, we understand your requirements and have you covered.



Tunnel & underpass luminaire

A durable yet sleek point source solution with maximum versatility

TunnelView is compatible with existing infrastructure for easy replacement of HID luminaires. Savings also add up with fast, simple installation, partnered with significantly less and easier servicing than traditional products, thus minimizing costly traffic disruptions.

Available in three sizes, multiple lumen packages, a complete array of optical distributions, and control/ connectivity options, this family is sure to make your job easier and exceed your expectations for all types of tunnel and underpass applications.

Also, on the off chance that TunnelView doesn't have the exact options you need, rest assured that we'll work with you on an "Engineered to Order" solution.

For further peace of mind, these luminaires are backed by Service Tag, which includes quick registration, access to luminaire configuration, and spare parts identification, for assistance throughout the life of the product.







Why point source lighting?

The advantages of point source lighting are the high luminous efficacy and the wider luminaire spacing that result in energy savings. Point source illumination is well suited for opposite and staggered arrangements which have two parallel lines of lighting fixtures that can mutually cast light on the center of the road, so it can focus light on the axis of the tunnel to improve uniformity. It is also effective when mounted overhead centering the tunnel. In the past, the threat of luminaire failure was a disadvantage of point source lighting, but the reliability and long life of LEDs minimize this issue.



Stainless steel hardware

All exposed screws are stainless steel with ceramic primer seal for high resistance to corrosion

2 Metal core board

Ensures greater heat transfer and longer lifespan

3 Glass lens

Offers IK09 impact protection

Durable construction

Rugged, anodized low copper die-cast aluminum housing for maximum durability in harsh environment

5 Secured door

Door is removable and secured with tether to prevent accidental dropping or disengagement

6 Heat sink

Built into the housing, ensures high efficacy and superior cooling by natural convection air flow pattern, always close to LEDs and driver optimizing their efficiency and life

1 LEDs + optics

High performance UV stabilized optical grade polymer refractor lenses to achieve desired distribution, optimized for maximum spacing, target lumens and lighting uniformity

8 Tool-less latches optional

Allows easy access, operable while wearing protective electrical gloves



Cast-in alignment guide

For ANSI wattage and source label



Service Tag

Signify's innovative way to provide assistance throughout the life of the product



Gasketing

Weather-proof gasketing for IP66 rated luminaire



Optional to add flexibility for now or in the future, luminaires ship with a protective cap






- · Three sizes for application flexibility
- · Lumen output ranges from 1,700 to 53,900
- Wattages from 20-459
- Nine optical distributions for maximum versatility
- · Color temperatures in 2700K, 3000K, or 4000K
- · Extensive mounting options from fixed or adjustable to swivel
- · Controls options: 0-10V Dimming, DALI, Sensor Ready, NYX Hemera ready
- · Service Tag is standard
- · Finish available in black, bronze, or gray





Dimensions and Optical Distributions





TULM (375mm) - 14-3/4" (375mm) - 121-7/8" (556mm)






Refer to specification sheets for additional dimensions.




Tunnel Distributions


SN Narrow




DK Type II Short



TW2 Type II Wall Mount



CBL Ceiling Counter Beam




Arrows indicate traffic direction


Underpass Distributions

R2M


Type II Medium




R3M Type III Medium




R3W Type III Wide



4 Type IV




Arrows indicate traffic direction



6 TunnelView and TubeLine

Mounting/Options & Accessories



Tunnel luminaire

A modular linear solution with a slim profile yet robust design

TubeLine provides outstanding linear lighting for any type of tunnel and is compatible with existing infrastructure. TubeLine is a very flexible tunnel lighting solution, and additional options like through-wiring of luminaires and remote driver boxes make it easy to create the perfect system.

Thanks to a wide range of optics and lumen outputs, TubeLine is configurable to suit any application needs. Designed for quick installation and low maintenance, TubeLine can help save you money and time. Control and connectivity options ensure that it's a futureproof investment for tunnels and underpasses.

The driver boxes of these luminaires are backed by Service Tag, which includes quick registration, access to luminaire configurations, and spare parts identification, for assistance throughout the life of the product.







1 Slim profile

Maximizes headroom and simplifies installation

2 Anodized aluminum finish

Provides corrosion resistance



Od1 fixed mounting bracket



Od2 fixed mounting bracket



Swivel mounting bracket

3 Tempered glass lens

Offers IK08 protection

4 Gasketing

Weather-proof gasketing for IP66 rated luminaire

5 Durable construction

Sturdy, factory sealed design, meeting 3G vibration

6 Direct mounted LEDs

LEDs are mounted directly to the large aluminum housing surface for superior cooling

7 Flying lead

For easy connection



Stainless steel hardware

All exposed screws are stainless steel with ceramic primer seal for high resistance to corrosion

Durable construction

Rugged low copper die-cast housing for maximum durability in harsh environments





Service Tag


Signify's innovative way to provide assistance throughout the life of the driver box



· Lumen output ranges from 3,200 to 18,000

Mounting Options and Dimensions


Luminaire



Refer to specification sheets for additional dimensions.



Driver Box




Junction box (JB1 / JB2) option for through wire and continuous row mounting



Optical Distributions

DTS


Distribution Symmetrical Standard



Arrows indicate traffic direction


DTS-WB

Distribution Symmetrical Wide




DTS-NB

Distribution Symmetrical Narrow



DTA


Distribution Asymmetrical Standard



Arrows indicate traffic direction


DTA-WB

Distribution Asymmetrical Wide



DTA-NB

Distribution Asymmetrical Narrow



Go to lumec.com/TubeLine to find out more.

Take control of your tunnel

Tunnel lighting systems must be very flexible and able to adapt to the changing environment, from day to night and from cloudy to sunny.

They are divided in many different lighting zones that each have their own specific requirements.

Controlling these zones is thus critical to safety. Lumec's luminaire and controls offering is designed to offer the greatest flexibly to fulfill any project need.

- 0-10V Dimming
- DALI drivers
- Twist-lock 7-pin receptacle
- · Sensor Ready (SR) drivers
- NYX-Hemera Ready

Lumec TunnelView and TubeLine luminaires are designed to work with Signify control systems or others in the market place, like NYX-Hemera.

For complete information on controls capabilities consult your local representative.





Turn your challenges into success stories

We understand that your lighting projects often bring unique requirements and need highly specialized solutions. Let us help.

While we offer a broad range of configurable products to meet your needs, nearly everything is customizable. Lumec works closely with you to design products and services around your specific needs through our "Engineered To Order" Program. Whether you need a special finish, or an entirely customized luminaire, we've got you covered.

We can make several levels of modifications, from simple to complex, whether for aesthetic or performance reasons. Leverage the knowledge and competencies of our organization to support your customers' projects. Trust in our leadership and quality as we work closely with you through every stage.

Contact your sales representative to start your customization journey today!



Luminaires you need from brands you trust

Signify understands the diverse needs of utility companies and the pressures you face to provide a reliable solution that will satisfy your customers' demands. Choose us, and make your job easier.

With a full portfolio of utility products and reliable industry brand names like Lumec, Gardco, and Hadco, Signify has a solution for all of your utility lighting needs. All of these high efficiency LED products are designed with the latest technology, are future proof with controls options and compatibility, and offer a broad range of lumen output and mounting options.

Lumec Roadway Cobraheads Off-Road RoadFocus RoadFocus Off-road Highmast **Security Lights** HighFocus Roadway Security Light (RSL) **Tunnel & Underpass TunnelView TubeLine**

Lumec Decorative

DuraForm

Gardco Floodlights



Domus

TownView

Hagerstown



© 2019 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone 800-668-9008