



Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

### Ordering Guide

Example: MUL4 N S7 LED2W

<b>Product Code</b>	MUL4	LED Brass Path light
<b>Finish</b>	N	Natural Brass
<b>Mounting</b>	S7	Mounting Stake
<b>LED</b>	LED2W	LED Lamp

### Specifications

#### HOUSING:

Solid brass stem. Die-cast brass. Roof has dual stainless steel hinge with stainless steel spring-lock for tool-less entry and relamping. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

#### FINISH:

Natural Brass (N) is as-cast and tumble polished.

#### OPTICAL ASSEMBLY:

Spun aluminum reflector with white thermoset powdercoat. Frosted tempered glass sprinkler shield includes top and bottom silicone gaskets for tight seal.

#### LAMPING:

Philips 12V LED 1.2W Capsule lamp. Up to 88% energy savins when compared to a 10W Capsule halogen lamp. Long lifetime of 15,000 hours (B50,L70). Operating temperature range is between -20C and 35C (ambient). Suitable for use in enclosed luminaires where the case temperature (Tc) remains below Tc MAX. Total Lumens = 105lm Lamp is included with fixture. Lower wattage lamps are acceptable.

#### ELECTRICAL ASSEMBLY:

Bi-pin socket type (G4) with 250° C high temperature teflon coated wire leads. 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

#### WARRANTY:

Five-year limited warranty.

#### CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

# MUL4 Path light

LED Brass

## Specifications

---

**Height :**

19 1/2" (495mm)

**Width:**

5 1/16" (129mm)

**Max. Weight:**

3.25

