

# Day-Brite

## CFI

by ignify

Linear

SLS Linkable strip



## Why choose one light, when you can get a team?

Discover how continuous rows of the Day-Brite / CFI SLS Linkable strip can give you the quality of light you need in hard-working spaces.

You have found just the right combination of dependability and flexibility for your light commercial or residential applications with the SLS Linkable strip. Whether mounting as a single unit or connecting multiple links for continuous rows, the compact design is ideal for areas such as garages, basements, coves, storage areas, workshops, or wherever task lighting is required. With Linkable strip you get the three "E's":

- Energy savings with the latest LED technology
- Extendable design, connect up to 15 Linkable strips together with seamless connectors
- Easy installation: mounting hardware, powercord and connectors are provided for simple mounting and wiring



# SLS Linkable strip

## Linear LED

### Great work comes from great workspaces.

- Ideal for commercial or residential applications
- Available in 2ft and 4ft lengths
- High efficacy, more than 100 lumens per watt
- Frosted acrylic lens for even, low glare lighting
- Damp location listed
- 5 year limited warranty




### Ordering guide

Example: SLS432L840-UNV

Series	Length (nominal)	Lumens <sup>1</sup> (nominal)	Color temp. (K)	Voltage
<div>SLS</div>	<div></div>	<div></div>	<div>840</div> –	<div>UNV</div>
SLS Linkable strip LED	2 2' length	16L 1600 lumens	840 80 CRI, 4000K	UNV Universal voltage 120–277V (non-dimmable)
	4 4' length	32L 3200 lumens		

<sup>1</sup> Nominal delivered lumens at 25°C ambient.

### Dimensions



All options are factory installed.

Many luminaire components, such as reflectors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants.

If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

