LIGHTOLIER

Downlighting

(F)

by (Signify

LyteCaster LED 3" Accent

L3SLW Square Wall Wash

Lightolier LyteCaster LED Accent wall wash features a 3.5" luminaire height that conserves plenum space without compromising performance. The modular and interchangeable light engine allows for an easy future upgrade. The accent wall wash is wet location listed and comes in 3 standard finish options.

Project:		
Location:		
Cat.No:		
Type:		
Lamps:	Qty:	
Notes:		

Complete product = Frame-in kit + Light engine + Trim Order each separately

Ordering guide: Frame-In kit

Example: L3AE1

Series	Frame type	Dimming	Input voltage
L3 LyteCaster 3" Accent	A AirSeal IC, New Construction, Screw AN AirSeal IC, New Construction, Nail C Remodeler Non-IC	E ELV/Triac dimming	1 120V
	N New Construction Non-IC	Z10 O-10V	U Universal (120-277V)

Ordering guide: Light engine

Example: L308830NF

Series L3	Lumens 08	CRI	ССТ	Beam	Option
L3 LyteCaster 3" Accent	08 800	8 80	27 2700K 30 3000K 35 3500K	NF Narrow flood F Flood	
		9 90	27 2700K 30 3000K ¹	NF Narrow flood F Flood	CW CrispWhite ¹

Ordering guide: Square trim


Example: L3SLWW

Series	Shape	Luminaire type	Flange
L3	S	LW	
L3 LyteCaster 3" Accent	S Square	LW Wall wash	W White A Aluminum




Square Wall Wash

Assembled configuration:




- LED Module Extruded Aluminum clear anodized finish heat sink with thermal interface material efficiently transfers heat away from LED. Includes strain relieved low voltage whip with snap interconnector for quick, tool less assembly of power connection. Tool-less assembly to trim.
- Mounting springs stainless steel mounting springs min 0.013" thick provide a universal mounting solution between the different frame offerings
- 4. Reflector: Aluminum Reflector.



- 6. Inner Aperture: Black to reduce glare. Chamber aperture reduces edge light flash.
- 7. Die Cast Aluminum Trim Flange.


Note: LED module allows for field replaceable optics. Order separately.




Square Wall Wash

L3AE1 & L3ANE1 new construction in IC AirSeal frame-in kits

Bottom view




Side view



Square trim

Side view



Light engine



Features

- 1. Housing: #23 ga. (.026") thick Galvanized steel. cULus listed for direct contact with thermal insulation (IC rated). AirSeal housing minimizes air leakage to less than 2 CFM at 1.57PSF (or 75PA), which complies with Title 24, the International Energy Conversation Code, and Washington State Energy Code (Section 502.4). This helps to reduce heat loss and condensation in ceiling. Internal access door for inspection of junction box.
- 2. Lower frame and top cover: #23 ga. (026") thick Galvanized steel. Accommodates ceilings up to 1" (25.4 mm) thick. Bottom cover provided with a .5" (6.2mm) lip and 4 embossed indicator lines to simplify alignment during installation. Housing can be locked into position on the mounting bars with locking screws.
- 3. Junction box: 2 ½" (64mm) x 5 3/8" (137mm) x 2" (51mm) #21 ga. (.032") thick galvanized steel, cULus listed 90 degrees C rated supply conductors. Rated for branch circuit wiring supplying connected luminaires (daisy
- 4. Mounting bars: #16 ga. (.059") thick galvanized steel. Bars pivot for easy attachment and wire in from below the ceiling line. Bars can extend to accommodate 16" (406mm) to 24" (610mm) O.C. joist spacing. Bars can accommodate 12" (305mm) O.C. joist spacing after slight field modification (see instruction sheet). Features integral selftapping screw phillips/square drive for attachment to wood or metal construction. Also available with integral nails (N). Attaches to T-bar ceilings without accessories. Bars installed on shortest dimension of frame can be easily rotated 90° from original position.
- 5. Electronic dimming driver:
 - Class 2 electronic LED Driver, with less than 1 second start up, RoHS compliant, suitable for damp locations. 120v 50/06Hz >.9 power factor. Sound rating Class "A" (<24dB). Complies with FCC,CFR title 47 part 15 Class B for EMI/RFI. Dimmable with standard electronic low voltage (ELV) & Triac dimmers. Dims to less than or equal to 10% of relative high output. 5 year limited warranty.
- 6. Ceiling cutout: 3 ¾" diameter.

Electrical

Input voltage 120v, Input freq.: 50/60 hZ, Input current .25 amps, Input Power 12W, Power factor >.9

Warranty

5 year limited warranty. (visit philips.com/warranties for details)


Labels

cULus type IC listed suitable for wet location. AirSeal.


Square Wall Wash

L3NZ10V New construction non IC 0-10V frame-in kit

Bottom view




Side view



Square trim

Side view



Light engine



Features

- 1. Non-IC housing: #23 ga. (.026") thick Galvanized steel. cULus listed for damp locations.
 AirSeal housing minimizes air leakage to less than 2CFM at 1.57 PSF (or 75PA), complies with Title 24, International Energy Conversation Code, and Washington State Energy Code (section 502.4) Frame provided with internal access door for inspection of junction box.
- 2. Lower frame and top cover:
 #23 ga. (026 ") thick Galvanized
 steel. Accommodates ceilings
 up to 1" (25.4 mm) thick. Bottom
 cover provided with a .5"
 (6.2mm) lip and 4 embossed
 indicator lines to simplify
 alignment during installation.
 Housing can be locked into
 position on the mounting bars
 with locking screws.
- 3. Junction box: 2 ½" (64mm) x 5 3/8" (137mm) x 2" (51mm) #21 ga. (.032") thick galvanized steel, cULus listed 90 degrees C rated supply conductors. Rated for branch circuit wiring supplying connected luminaires (daisy chaining).
- 4. Mounting bars: #16 ga. (.059") thick galvanized steel. Bars pivot for easy attachment and wire in from below the ceiling line. Bars can extend to accommodate 16" (406mm) to 24" (610mm) O.C. joist spacing. Bars can accommodate 12" (305mm) O.C. joist spacing after slight field modification. (see instruction sheet) Features integral selftapping screw phillips/square drive screws for attachment to wood or metal construction. Attaches to T-bar ceilings without accessories Bars installed on shortest dimension of frame can be easily rotated 90° from original position.
- 5. Electronic dimming driver: Class 2 electronic LED driver, RoHS compliant, suitable for damp location. 120/277v 50/06Hz >.9 power factor. MTP (module thermal protection) current cutback up to 10% to prevent overheating. Sound rating Class "A" (<24dB). Complies with FCC, CFR title 47 part 15 Class A for EMI/RFI. Dimming Protocol (0–10v). Dims to less than or equal to 10% of relative high output.
- 6. Ceiling cutout: 3 3/4" diameter.

Electrical

Input voltage: 120/277, input freq.:50/60hZ. Input current .14A/.06A Input Power 16.4W, Power factor >.9

Warranty

5 year limited warranty. (visit philips.com/warranties for details)


Labels

cULus listed suitable for wet location. AirSeal. Inherently Protected. IP rated.


Square Wall Wash

L3CE1 Non-IC Remodeler kit

Bottom view




Side view



Square trim

Side view



Light engine



Features

- 1. Non-IC housing: #25 ga. (025") thick Galvanized steel. Provided with 2 plates steel retaining springs that can accommodate ceiling thickness up to 1" (25.4mm) thick. Philips screw driver required to tighten springs that secure housing to ceiling.
- 2. Junction box: #22 ga. (.034") thick Galvanized steel. cULus ,suitable for damp locations. Junction box assembly swivels for tight plenum spaces. Snap off cover permits wiring access.
- 3. Electronic dimming driver (same as new construction): Class 2 electronic LED Driver, with less than 1 second start up, RoHS compliant, suitable for damp locations. 120v 50/06Hz ».9 power factor. Sound rating Class "A" (<24dB). Complies with FCC,CFR title 47 part 15 Class B for EMI/RFI. Dimmable with standard electronic low voltage (ELV) & Triac dimmers. Dims to less than or equal to 10% of relative high output. 5 year limited warranty.
- Trim compatibility: Not compatible with adjustable trims except for L3RG series Gimbals.
- 5. Ceiling cutout 3 ¾" diameter.

Electrical

Input voltage 120v, Input freq.: 50/60 hZ, Input current .25 amps, Input Power 12W, Power factor >.9

Warranty

5 year limited warranty. (visit philips.com/warranties for details)

Labels

cULus listed suitable for wet location, inherently protected (IP rated).

Square Wall Wash

Electrical Specifications

Frame-in kit	Input volts	Input freq.	Input current	LED drive current	Input power	LED power	THD factor	Power factor
L3AE1	120V	50/60Hz	.090 A	260 ma	10.64 W	8.76 W	<20%	> .9
L3ANE1	120V	50/60Hz	.090 A	260 ma	10.64 W	8.76 W	<20%	> .9
L3CE1	120V	50/60Hz	.090 A	260 ma	10.64 W	8.76 W	<20%	> .9
L3NZ10U	120V	50/60Hz	.102 A	260 ma	11.8 W	9.74 W	<10%	> .8
L3NZ100	277V	50/60Hz	.047 A	260 ma	11.8 W	8.90 W	<10%	> .8

Lensed wall wash

Lighting Data - Example

P4RD10NZ10UVB/P4RD835VB/P4RLWCL illumination on the wall 4^{\prime} down from the ceiling is 15 f.c. beneath and 16 f.c. between fixtures.


Adjustment factors

Color temperature (CCT)

2700K =	88%
3000K =	96%
3500K =	100%

Color Rendering Index (CRI)


80 =	100%
90 =	85%
90 (CW) = Crisp White	78%



Square Wall Wash

Beam spread: Narrow flood

Candela Curve



Frame: L3NZ10U Light engine: L308835NF Trim: L3SLWA

Output lumens:	344lms
Input Watts1:	11.8 W
Efficacy:	29.2lm/w
CCT ² :	3500 K
CRI:	>80

Report no³: 536GFR

Multiple unit data

Muttiple unit data				
Foot- candles	2' from wall			
on wall	→ ₃	3' on center		
1	13	9	13	
₩ 2	14	12	14	
± 3	10	10	10	
-	7	7	7	
Distance from ceiling in feet C 0 6 8 2 9 5 7 8 6 7	5	5	5	
9 6	4	4	4	
E 7	3	3	3	
± 8	3	3	3	
ğ 9	2	2 2	2	
뚱 10	2	2	2 2	
i≘ 12	2	1	2	
14	1	1	1	

Multiple unit data

mattipic unit data			
Foot- candles	3' from wall		ıll
on wall	3' on center		
1	5	5	5
teet 2	9	9	9
± 3	9	9	9
	8	8	8
<u>≓</u> 5	6	6	6
Distance from ceiling in feet Cl Ol 6 8 L 9 G F E 7 Cl Ol 6 8 L 9 G F E 7	5	5	5
E 7	4	4	4
£ 8	3	3	3
ğ 9	3 3 2 2 2	3	3
뚱 10	2	2	2
i 12	2	3 2 2 2	2
14	2	2	2


Multiple unit data (shown above)

Foot- candles	3' from wall			
on wall	2	4' on center		
1	5	4	5	
₩ 2	7	6	7	
و ع و	7	6	7	
.≒ 4	6	6 6 5	6	
<u>≓</u> 5	5	5	5	
om ceiling in feet 2 3 4 5 6 7	4	4	4	
E 7	3	3	3	
£ 8	3	3	3	
Distance from ceiling in feet 5 10 6 8 2 9 5 7 8 6 7 8 9 10 15	3 2 2	4 3 3 2 2 2	2	
FS 10	2	2	2	
i 12	2	2	2	
14	1	1	1	

Beam spread: Flood

Candela Curve

side



side

Frame: L3NZ10U Light engine: L308835F Trim: L3SLWA

Output lumens:	351lms
Input Watts ¹ :	11.8 W
Efficacy:	29.7lm/w
CCT ² :	3500 K
CRI:	>80

Report no³: 525GFR

Multiple unit data

Foot- candles	2' from wall		
on wall	3' on center		
1	13	9	13
teet 2	14	12	14
و ع و	10	10	10
.≒ 4	7	7	7
i guil 5	5	5	5
9 6 E 7	4	4	4 3 3
E 7	3	3	3
£ 8	3	3	3
Distance from ceiling in feet Cl Ol 6 8 L 9 G b 8 C Cl Ol 6 8 L 9 G b 8 C	4 3 3 2 2 2	2	2 2 2
E 10	2	2	2
i≘ 12	2	1	2
14	1	1	1

Multiple unit data

Muttiple unit data						
Foot- candles		3' from wall				
	wall	3' on center				
	1	6 9	5	6		
ŧ	2	9	8	9 9		
ę	3	9	9	9		
.⊨	4	8	8	8		
Ë	5	6	6	6		
Distance from ceiling in feet	2 3 4 5 6 7 8 9	5	5	6 5 4 3 3		
шc	7			4		
Ē	8	4 3	4 3	3		
ű	9	3	3	3		
sta	10		3	3		
Ö	12	2 2	3 2 2	2 2		
	14	2	2	2		

Multiple unit data (shown above)

mattipie aint data (onominacore)						
Foot- candles	3' from wall					
on wall	5	1' on cente	er 📥			
1	5	4	5			
₩ 2	7	6	7			
Distance from ceiling in feet 0 6 8 2 9 5 7 8 6 7 8 6 7 8 7 8 7 8 7 8 7 8 7 8 7 8	7	6	7			
.⊨ 4	6	6	6			
<u>≓</u> 5	5	5	5			
ම 6	4	4	4			
E 7	3	3	3			
£ 8	3	3	3			
ğ 9	2 2	2	2 2 2			
5 10	2	2 2 2	2			
i 12	2	2	2			
14	1	1	1			

