

Day-Brite

CFI

by Signify

Special Application

CRG series recessed grid

Cleanroom
T5, T5HO, or T8



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

The Day-Brite / CFI CRG series recessed grid troffer is a cleanroom luminaire with hinged door designed to meet the criteria for critical environments in recessed mount applications.

Ordering guide

Example: **CRG24-454HO-UNV-A-2/2-EB**

Family	No. of Lamps	Lamp Type ¹	Voltage	Lens Type	No. of Ballasts	Ballast Type	Options	
CRG14	1x4	2 Two lamps	UNV Universal voltage, 120-277V	A .125 Prismatic Acrylic	1/2 One 2 lamp ballast	EB Electronic ballast, <10% THD, T8 instant start, T5 rapid start	E7 B60 emerg. ballast, T8, 600-700 lumens, 120/277V ²	
CRG22	2x2	3 Three lamps		B .125 DR Prismatic Acrylic	1/3 One 3 lamp ballast		EB1OR Electronic ballast, T8 rapid start, <10% THD	E5 B50 emerg. ballast, U.S. or Canada market, T8, 1100-1400 lumens, UNV ³
CRG24	2x4	4 Four lamps (2x2 & 2x4)		C .140 DR Prismatic Acrylic				1/4 One 4 lamp ballast
		6 Six lamps (2x4)	24HO 24WT5HO (24")	2/1 Two 1 lamp ballasts	2/2 Two 2 lamp ballasts	E6LP LP600 emerg. ballast U.S. or Canada market, T5/T5HO, 750-1325 lumens, 120/277V ^{2,3}		
			28 28WT5 (48")			2/3 Two 3 lamp ballasts	1/21 2 lamp & 1 lamp ballasts	SS Stainless steel housing, brushed stainless steel door
			32 32WT8 (48")	1/42 4 lamp & 2 lamp ballasts				SSD stainless steel door
			54HO 54WT5HO (48")		UV .007 UV Absorbing Overlay	AG Agion™ antimicrobial protection in powder coat paint (white finish only)		
							GLR Fusing, fast blow	
					NLF7 7W PL Night Light ^{2,3}			NLF7 7W PL Night Light ^{2,3}
						NLEDS LED nightlight ³ (120V only)	NLEDS LED nightlight ³ (120V only)	

Footnotes

- Lamps supplied by others.
- Specify voltage.
- Limited availability in 2 ft. luminaire. Consult factory.

General Notes

• Many luminaire components, such as reflectors, refractors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.



CRG Recessed grid troffer

Cleanroom, T5, T5HO, or T8

Standards

- ETL (US/Canada) Wet Location listed.
- Suitable for Class 100, 1,000, 10,000, 100,000 environments.
- NSF2 Food Zone/Non-Contact and Splash Zone.

Construction/Finish

- 18-gauge cold rolled steel "hole-free" housing with welded seams. Optional stainless steel or aluminum housing available.
- 18-gauge one-piece cold rolled steel door with concealed pin hinges. Optional brushed stainless steel or aluminum door available.
- Captive stainless steel Phillips flat head fasteners are standard.
- Standard baked white polyester powder coat paint finish. Multi-stage pretreatment process. Salt spray 1,000 hours.

Lens

- Standard .125" prismatic acrylic lens with smooth side exposed to facilitate cleaning. Optional lensing shown below.
- Continuous formed channels for positive lens retention.
- Lens and door sealed with closed cell neoprene sponge door and lens gasketing.

Electrical

- Standard Class P, sound rated A electronic ballast. Other ballast options available.


Installation

- Housing to fit 1" or 1-1/2" grid ceilings. Support above plenum by others.
- Flattened 7/8" knockouts in top and ends of housing.

Option

- Agion™ Antimicrobial protection using silver technology inhibits bacterial colonization on metal interior and exterior surfaces. Agion™ antimicrobial FDA recognized and EPA registered, meeting all applicable EPA standards. Only available with standard white finish.

Dimensions



Size	A	B	C	D	E	F
14	48"	32"	10.375"	12"	11.688"	5"
22	23.875"	16"	22.375"	24"	23.688"	4.5"
24	48"	32"	22.375"	24"	23.688"	4.5"



Some luminaires use fluorescent or high intensity discharge (HID) lamps that contain small amounts of mercury. Such lamps are labeled, "Contain Mercury" and/or the symbol "HG". Lamps that contain mercury must be disposed of in accordance with local requirements. Information regarding lamp recycling and disposal can be found at www.lamprecycle.org

