





Coreline Trunking LL120X 1xPSD 9



Mounting instructions

Instructions de montage
Montageanleitung
Montage instructie
Istruzioni di montaggio

Instrucciones de montaje
Instruções de montagem
Monteringsinstruktioner
Monteringsvejledning

Kokoonpano- ja kiinnitysohjeet
Montaj yönergesi
Szerelési utasítások
Instrukcja montażu


Návod k montáži
Návod k montáži




~220V...240V
50 Hz/60 Hz



IP20



LL120Z MB-SW 2xEP CU9 WH



Luminaire type	Max No. of luminaires on MCB (16A type-B)		Inrush Current Peak [A/μs]
	PSD	No driver + PSD	PSD
LL120X	12	15	4,8/2300

$I_{L1max} = I_{L2max} = I_{L3max} = 16A$ (MCB B type)
Max current load of each phase line in luminaire.


AWARE! LET SHORTCUT DALI INTERFACE IF NOT USED

Luminaire type		SYSTEM FLUX	Wattage	Ta	A [m]	L1 [m]	kg max
LL120X	LED90S/840	9000	64	-20°C to +35°C	3,45	0,50 - 0,80	7,5
	LED160S/840	16000	108	-20°C to +35°C			
LL120X O	LED84S/840	8400	64	-20°C to +35°C	3,45	0,50 - 0,80	7,5
	LED150S/840	15000	108	-20°C to +35°C			




12NC 4427 102 21704
Versiondate: 21/06/2017
Data subject to change without notice
Printed in Poland
www.philips.com/lighting

PHILIPS



9x1,5 mm² or
9x2,5 mm²



[SP] - Select phase (factory setting is L1)

