

Day-Brite

CFI

by  Signify

Recessed

FluxPanel gen 2

Flat panel



Even illumination, at the right price



The unfailing choice for lasting confidence. FluxPanel luminaires are in their second generation, which means more experience behind the product. Backed with more than 125 years of lighting expertise, Day-Brite has the knowledge and expertise to bring you a panel that you can count on.

Benefits

- Immerse users in comfortable, welcoming spaces that are free of glare and distractions; with color that remains consistent across luminaires and over time.
- Available with an integrated Interact sensor for wireless lighting control
- Rely on one flat panel LED luminaire family for multiple applications - recessed, surface, or suspended.
- NSF rating (for Non-Food Zone and Splash Zone Applications) is offered as standard allowing FluxPanel to be used in food service processing facilities and other areas with high sanitization needs
- Maximize your investment with rebate eligible panels in both DLC standard and premium categories (see the DLC QPL list for exact catalog numbers www.designlights.org/QPL).

Not all product variations listed on this page are DLC qualified. To ensure that a specific model is qualified, visit www.designlights.org/search



interact
ready.

FPZ FluxPanel LED gen 2

1x4, 2x4 & 2x2 recessed luminaires

Affordable doesn't have to mean cheap

FluxPanel luminaires are ideal for office, healthcare and educational facilities that seek to minimize hassles, meet sustainability goals, and maximize return on investment. With DLC standard and DLC Premium versions available, there's a panel for every project and every budget. Maximize your rebate potential with the configuration that suits your energy and lighting needs best.



When a good deal matters, put your trust in FluxPanel luminaires. For more information visit www.day-brite.com.

Ordering guide

Standard configurations available with all choices, unless otherwise noted. **Base configurations selections indicated by blue.** example: **1FPZ38L840-4-ADS-UNV-DIM-BSL6LST**

Family	Lumens (nom.)	CRI/CCT	Length	Diffuser	Voltage	Dimming driver	Options ²
1FPZ FluxPanel 1ft gen 2	38B ⁴ 3800lm	835 80CRI/3500K	4	DS	UNV Universal,	DIM ¹	F1 3/8" flex, 18 ga. 6'; 3 leads (hot, neutral, ground) F2 3/8" flex, 18 ga. 6'; 4 leads (2 hots, neutral, ground) F1/D ⁸ 3/8" twin flex, 18 ga. 6' for dimmable luminaires; Flex 1: 3 leads (hot, neutral, ground) Flex 2: 2 leads (Dim+/Dim-) F2/5W ⁸ 3/8" single flex, 18 ga. 6' for dimmable luminaires; 5 leads (hot, neutral, ground, Dim+/Dim-) F2/6W ⁸ 3/8" single flex, 18 ga. 6' for dimmable & EM luminaires; 6 leads (2 hot, neutral, ground, Dim+/Dim-) GLR Fusing, fast blow DSC Quick driver disconnect CHIC Chicago Plenum rated BAC Meets the requirements of the Buy American Act of 1933 (BAA) (see FLP spec sheets for all BAA details and restrictions) ER100 ^{4,5,11,12} UL924 listed sensor bypass relay, factory installed between driver & sensor BSL10LST ^{5,9,14} Bodine 10W battery pack BSL6LST ^{5,9,14} Bodine 6W battery pack SWZCSR ^{1,4,7,9,10} Remote Interact wireless sensor with integral daylight & occupancy sensing, advanced grouping w/dwell time SWZCS ^{1,4,9,10,14} Interact wireless sensor with integral daylight & occupancy sensing, advanced grouping w/dwell time RADIO ^{1,4,5,7,9} Interact RF sensor for wireless connectivity only (no sensing)
	15L 1500lm 30L 3000lm 38L 3800lm 45L 4500lm 50L 5000lm	840 80CRI/4000K 850 80CRI/5000K	4ft	ADS Acrylic Diffuse A12 Diffuse (Prismatic)	120 ³ 120V 277 277V 347 347V	0-10V SDIM ⁶ Step to 30% input power XDIM ^{3,6} MarkX phase	
Other packages may be ordered in increments of 100 from 1500lm to 5000lm							
2FPZ FluxPanel 2ft gen 2	38B ⁴ 3800lm	835 80CRI/3500K	2	DS	UNV Universal,	DIM ¹	F1 3/8" flex, 18 ga. 6'; 3 leads (hot, neutral, ground) F2 3/8" flex, 18 ga. 6'; 4 leads (2 hots, neutral, ground) F1/D ⁸ 3/8" twin flex, 18 ga. 6' for dimmable luminaires; Flex 1: 3 leads (hot, neutral, ground) Flex 2: 2 leads (Dim+/Dim-) F2/5W ⁸ 3/8" single flex, 18 ga. 6' for dimmable luminaires; 5 leads (hot, neutral, ground, Dim+/Dim-) F2/6W ⁸ 3/8" single flex, 18 ga. 6' for dimmable & EM luminaires; 6 leads (2 hot, neutral, ground, Dim+/Dim-) GLR Fusing, fast blow DSC Quick driver disconnect CHIC Chicago Plenum rated BAC Meets the requirements of the Buy American Act of 1933 (BAA) (see FLP spec sheets for all BAA details and restrictions) ER100 ^{4,5,11,12} UL924 listed sensor bypass relay, factory installed between driver & sensor BSL10LST ^{5,9,14} Bodine 10W battery pack BSL6LST ^{5,9,14} Bodine 6W battery pack SWZCSR ^{1,4,7,9,10} Remote Interact wireless sensor with integral daylight & occupancy sensing, advanced grouping w/dwell time SWZCS ^{1,4,9,10,14} Interact wireless sensor with integral daylight & occupancy sensing, advanced grouping w/dwell time RADIO ^{1,4,5,7,9} Interact RF sensor for wireless connectivity only (no sensing)
	20L 2000lm 30L 3000lm 38L 3800lm 45L 4500lm 54L 5400lm	840 80CRI/4000K 850 80CRI/5000K	2ft	ADS Acrylic Diffuse A12 Diffuse (Prismatic)	120 ³ 120V 277 277V 347 347V	0-10V SDIM ⁶ Step to 30% input power XDIM ^{3,6} MarkX phase	
Other packages may be ordered in increments of 100 from 2000lm to 5400lm							
2FPZ FluxPanel 2ft gen 2	38B ⁴ 3800lm	835 80CRI/3500K	4	DS	UNV Universal,	DIM ¹	F1 3/8" flex, 18 ga. 6'; 3 leads (hot, neutral, ground) F2 3/8" flex, 18 ga. 6'; 4 leads (2 hots, neutral, ground) F1/D ⁸ 3/8" twin flex, 18 ga. 6' for dimmable luminaires; Flex 1: 3 leads (hot, neutral, ground) Flex 2: 2 leads (Dim+/Dim-) F2/5W ⁸ 3/8" single flex, 18 ga. 6' for dimmable luminaires; 5 leads (hot, neutral, ground, Dim+/Dim-) F2/6W ⁸ 3/8" single flex, 18 ga. 6' for dimmable & EM luminaires; 6 leads (2 hot, neutral, ground, Dim+/Dim-) GLR Fusing, fast blow DSC Quick driver disconnect CHIC Chicago Plenum rated BAC Meets the requirements of the Buy American Act of 1933 (BAA) (see FLP spec sheets for all BAA details and restrictions) ER100 ^{4,5,11,12} UL924 listed sensor bypass relay, factory installed between driver & sensor BSL10LST ^{5,9,14} Bodine 10W battery pack BSL6LST ^{5,9,14} Bodine 6W battery pack SWZCSR ^{1,4,7,9,10} Remote Interact wireless sensor with integral daylight & occupancy sensing, advanced grouping w/dwell time SWZCS ^{1,4,9,10,14} Interact wireless sensor with integral daylight & occupancy sensing, advanced grouping w/dwell time RADIO ^{1,4,5,7,9} Interact RF sensor for wireless connectivity only (no sensing)
	15L 1500lm 30L 3000lm 38L 3800lm 43L 4300lm 48L 4800lm 54L 5400lm 60L 6000lm 74L 7400lm 80L 8000lm	840 80CRI/4000K 850 80CRI/5000K	4ft	ADS Acrylic Diffuse A12 Diffuse (Prismatic)	120 ³ 120V 277 277V 347 347V	0-10V SDIM ⁶ Step to 30% input power XDIM ^{3,6} MarkX phase	
Other packages may be ordered in increments of 100 from 1500lm to 8000lm							

FPZ FluxPanel LED gen 2

1x4, 2x4 & 2x2 recessed luminaires



1. Integral control options dimmable to 1% via wireless wall switch.
Non-controls options 0-10V dim to 1% for standard and 5% for base configs.
2. All options only available with standard configurations.
3. XDIM is 120V only.
4. Specify DIM driver option only.
5. Not available with 347V option.
6. XDIM max lumen output 50L: <45L requires ELV dim; >45L requires Triac dim.
7. Not available with surface or suspended accessories.
8. Flex with dimming not available with Interact sensors.
9. Emergency and Interact options not clean room certified, nor NSF listed.
10. Must order IRT9015 Interact commissioning remote with each system order.
11. Must be installed in conjunction with a UL1008 device.
12. Must be ordered with an integral controls option.
13. Consult Signify to confirm whether specific accessories are BAA-compliant.
14. Specify ADS diffuser for integrated sensor or EM test switch.

Update Accessories¹³

FMA14FP: 1'x4' "F" mounting frame for NEMA "F" mounting
FMA22: 2'x2' "F" mounting frame for NEMA "F" mounting
FMA24: 2'x4' "F" mounting frame for NEMA "F" mounting

Surface mount field assembly kit (field assembled)

FSF14: 1'x4' **FSF22:** 2'x2' **FSF24:** 2'x4'

Surface mount field install kit (factory welded seams)

FSK22: 2'x2' **FSK24:** 2'x4'

Adj. cable hanger kit with straight white 18/5 cord for dimming (two-1 powered, 1 non-powered).
FPZCH48-1D-SC-UNV: 120/277V
FPZCH48-1D-SC-347: 347V

IRT9015: handheld remote for grouping and configuration (at least one remote required for any SWZCS installation).



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 800-555-0050

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.