

# HADCO

by  Signify

Urban

Bracket arm

249PL Arm bracket


Project: \_\_\_\_\_  
Location: \_\_\_\_\_  
Cat.No: \_\_\_\_\_  
Type: \_\_\_\_\_  
Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
Notes: \_\_\_\_\_

## Ordering Guide

Example: 249PL ABS 50H E

Product Code	249PL	Bracket Arm	
Finish	ABS	Antique Brass	
	ACP	Antique Copper	
	ARD	Antique Red	
	ASI	Antique Silver	
	BLK	Black	
	BRN	Brown	
	BRZ	Bronze	
	FGN	Forest Green	
	GRA	Granite	
	IRN	Ironstone	
	RBZ	Rustic Bronze	
	SRT	Shadow Rust	
	VBZ	Verde Bronze	
	VCP	Verde Copper	
	VGN	Verde	
	VTC	Vintage Copper	
Wattage/Source	WBZ	Weathered Bronze	
	WHT	White	
	50H	50W MH	*1
	35S	35W HPS	*1
	50S	50W HPS	*1
	70S	70W HPS	
Voltage	100S	100W HPS	
	150S	150W HPS	*1
	150I	150W INC.	*1
	E	120V	
	F	208V	
	G	240V	
	H	277V	

\*1 (E) 120V option only



## Specifications

### CONSTRUCTION:

2" dia. x .125" Wall aluminum tubing welded to 2" I.D. splicing fitter and 4" I.D. post fitter. Cast aluminum 2" I.D. splicing fitter welded to bent arm. Cast aluminum 4" I.D. post fitter.

### FINISH:

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

### BALLAST:

Post line ballast supplied with mounting hardware. (Contact factory for ballast selection.)

### MOUNTING:

Fixture mounts to 4" I.D. post. Wire and wire nuts supplied for attaching to lantern and incoming power supply.

### WARRANTY:

Three-year limited warranty.

# 249PL Bracket arm

## Arm bracket

### Specifications

---

**Height:**

50"

**Width:**

27 7/8"

**Max. Weight:**

