





## Inexpensive Ethernet integration


The Philips Dynalite PDEB provides a standard Ethernet connection to a Philips lighting control system in applications ranging from tunnels to hotel rooms. It provides bridging functionality between an Ethernet backbone and DyNet devices.

## **PDEB**

## Inexpensive Ethernet integration

- Powerful custom task engine Allows users or third-party systems to run macros such as 'After Hours', 'Shut Down', 'Welcome' and more.
- **Versatile mounting options** Hybrid mounting clips allow the device to be mounted on a DIN-rail or to any flat surface

## **Dimensions**



 $\begin{tabular}{ll} Specifications \\ Due to continuous improvements and innovations, specifications may change without notice. \\ \end{tabular}$ 



#### **Electrical**

Supply Type	DyNet or DC*
Supply Voltage	12-24 VDC†
DC Supply Current	300 mA @ 12 V 250 mA @ 24 V
DyNet Supply Current	100 mA @ 12 V 50 mA @ 24 V
DyNet DC Output Current <sup>‡</sup>	200 mA
IEC Overvoltage Category	III
Control	
Communication Ports	1 x RS-485 1 x Ethernet (10/100 baseT)
Supported Protocols	DyNet DMX TCP/IP (TCP, UDP) IPv4, IPv6
Dry Contact Inputs	1 (AUX)
User Input	1 x service switch
Indicators	1 x service LED

- From external regulated SELV / Class 2 supply
- Power supply voltage shall match network voltage
- If powered by external SELV / Class 2 supply

#### **Physical**

106 x 110 x 38 mm (4.17 x 4.33 x 1.50 in)
0.21 kg (0.46 lb)
Low profile DIN-rail polycarbonate (6 unit)
1 x RJ45 1 x RJ12 1 x 6-way pluggable screw terminal
,, ,,
ctor Size 2.5 mm² (#12 AWG) (max)
1 x 2-way pluggable screw terminal
2.5 mm² (#12 AWG) (max)
-20° to 50°C ambient (-4° to 122°F)
-25° to 70°C ambient (-13° to 158°F)
0 to 90% non-condensing
II
CE, RCM, UL/cUL, FCC, ICES, UKCA, RoHS

\*\* For indoor installation only











## **Electrical**

### SELV/CLASS 2 supply with full DyNet load



#### **DyNet supply**



# Ordering Code Product

Product	Philips 12NC
PDEB	913703240009
Accessories	
DDNP1501 (12 VDC network power supply)	913703090309
DMNP24040-P-NA (24 VDC network power supply)	913703580309



<sup>© 2022</sup> Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Revision 08 2021-09-09 www.dynalite.com