

PHILIPS

Candle & Lustre

LED

1.7W-15W

E14

Warm White

8718696730201



State-of-the-art LED light bulb for the home

This Philips LED light bulb provides a beautiful, extra warm light, an exceptionally long life, and immediate, significant energy savings. With its flame color temperature, this light bulb is the perfect choice for a cozy atmosphere.

Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Light beyond illumination

- For use in refrigerators and freezers

Highlights

Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Special purpose appliance bulb

Philips refrigerator bulbs can be used in refrigerators, freezers, and similar places subject to low operating temperatures. Easily replace your appliance bulbs with a Philips refrigerator bulb for a long, useful life.

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: E14
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 5.9 cm
- Weight: 0.014 kg
- Width: 2.5 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 240 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 150 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 827 | CCT of 2700K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 20 mA
- Efficacy: 88.2352941176471 lm/W

Packaging information

- EAN: 8718696730201
- EOC: 871869673020100
- Product title: LED 15W T25 E14 827 FR ND 1BC/3_AU

Power consumption

- Power factor: 0.4
- Voltage: 220–240 V
- Wattage: 1.7 W
- Wattage equivalent: 15 W
- Energy Efficiency Label (EEL): A++

Product dimensions & weight

- Length: 5.9 cm

Rated values

- Rated beam angle: 240 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 150 lumen
- Rated power: 1.7 W

Technical specifications

- Frequency: 50–60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718696730201
- Net weight: 0.020 kg
- Gross weight: 0.032 kg
- Height: 14.600 cm
- Length: 3.000 cm
- Width: 9.000 cm
- Material number (12NC):
929001325769



Issue date: 2021-05-03
Version: 0.140

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com