

# PHILIPS

Reflector

LED

1.8W-30W

E14

Warm White

8718699675332



## A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### High quality light

- No visible flicker

### Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

### Create the right light for your home

- A simple LED for everyday use

# Highlights

## No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because

Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

## A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E14
- Technology: LED

## Bulb dimensions

- Height: 6.5 cm
- Weight: 0.04 kg
- Width: 3.9 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 36 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 150 lumen
- Starting time: 0.1 s
- Warm-up time to 60% light: Instant full light
- Color Code: 827 | CCT of 2700K

## Other characteristics

- Lamp current: 16 mA
- Efficacy: 105 lm/W

## Packaging information

- EAN: 8718699675332
- EOC: 871869967533200
- Product title: LEDspots 1.8-30W R39 827 E14

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 1.8 W
- Wattage equivalent: 30 W

## Product dimensions & weight

- Length: 6.5 cm

## Rated values

- Rated beam angle: 36 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 150 lumen
- Rated peak intensity: 250 cd
- Rated power: 1.8 W

## Technical specifications

- Frequency: 50-60 Hz

## Packaging dimensions & weight

- EAN/UPC - product: 8718699675332
- Net weight: 0.030 kg
- Gross weight: 0.037 kg
- Height: 6.700 cm
- Length: 4.000 cm
- Width: 4.000 cm
- Material number (12NC): 929001890991



Issue date: 2022-07-19  
Version: 0.16

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)