

PHILIPS

Bulb

LED

8W-68 (68W GLS, 13W CFL)W

E27

Cool Daylight

8718699688042



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- No visible flicker

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Create the right light for your home

- A simple LED for everyday use

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because

Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 11 cm
- Weight: 0.049 kg
- Width: 6 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 200 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 770 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 865 | CCT of 6500K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 72 mA
- Efficacy: 96 lm/W

Packaging information

- EAN: 8718699688042
- EOC: 871869968804200
- Product title: LEDBulb 8W E27 6500K 230V 2PF/3 AU

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 8 W
- Wattage equivalent: 68 W

Product dimensions & weight

- Length: 11 cm

Rated values

- Rated beam angle: 200 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 770 lumen
- Rated power: 8 W

Technical specifications

- Frequency: 50-60 Hz

**Packaging dimensions and weight
[LEDBulb 8W E27 965 230V 2PF/3
AU]**

- EAN/UPC - product: 8718699688042
- Net weight: 0.084 kg
- Gross weight: 0.109 kg
- Height: 10.700 cm
- Length: 6.200 cm
- Width: 10.000 cm
- Material number (12NC):
929003007319

**Packaging dimensions and weight
[LEDBulb 8W E27 6500K 230V 2PF/3
AU]**

- EAN/UPC - product: 8718699688042
- Net weight: 0.084 kg
- Gross weight: 0.109 kg
- Height: 10.700 cm
- Length: 6.200 cm
- Width: 10.000 cm
- Material number (12NC):
929001915519



Issue date: 2022-07-21
Version: 0.161

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.