

# PHILIPS

Bulb

LED

9W-70W

Cool Daylight

8718699693626



## State-of-the-art LED light bulb for the home

Philips LED light bulbs provide a beautiful, cool white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### Choose a simple replacement for your old bulbs

- Perfect fit and high-quality finishing

### Choose for a sustainable solution

- Safe for any room and convenient to recycle
- You can trust what the Philips packaging is saying.

### Light beyond illumination

- A simple LED for everyday use
- 3 hours of emergency lighting
- Automatic recharge when switched ON

# Highlights

## Perfect fit

With a familiar shape, these bulbs are the perfect fit for your existing fixtures. They look just like the classic light bulb.

## No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

## A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

## 3 hours of emergency lighting

You can rely on this emergency bulb for 3 hours of battery powered light. Ideal for power outages and is automatically recharged from the mains when switched on.

## Automatic recharge when switched ON

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Other
- Socket: B22
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 13.8 cm
- Weight: 0.15 kg
- Width: 7 cm

## Durability

- Average life (at 2.7 hrs/day): 10 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 10,000 hour(s)
- Number of switch cycles: 5,000

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 900 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Color Code: 865 | CCT of 6500K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 50 mA
- Efficacy: 100 lm/W

## Packaging information

- Product family: LED
- EAN: 8718699693626
- EOC: 871869969362600
- Product title: Inverter LED lamp 9W CDL B22

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 9 W

## Product dimensions and weight

- Length: 9.7 cm

## Rated values

- Rated luminous flux: 900 lumen
- Rated power: 9 W

## Technical specifications

- Frequency: 50 Hz

**Packaging dimensions and weight**

- EAN/UPC - product: 8718699693626
- Net weight: 0.125 kg
- Gross weight: 0.160 kg
- Height: 14.200 cm
- Length: 7.100 cm
- Width: 7.100 cm
- Material number (12NC): 929002237513



Issue date: 2023-11-08  
Version: 0.159

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)