

LUMEC

by Signify

Succeed in your roadway lighting design goals

Roadway

RoadView





Versatile performance

Innovative solutions

The Lumece RoadView LED roadway luminaires were created to help those responsible for lighting our streets and highways succeed in their lighting design goals. Powered by the LEDGINE LED platform, and featuring innovative thermal management design, the RoadView offers exceptional performance and value. This versatile luminaire can be tailored to the unique specifications of each project by offering multiple LED boards and wattage options.

Sustainable performance

Utilizing LEDGINE Platform drivers the RoadView provides exceptional energy efficiency. This luminaire is manufactured with fully recyclable aluminum castings and extrusions that help to protect our environment for years to come. Energy efficiency is enhanced with optional dimming, programmable drivers, and outdoor control systems.



LEDGINE LED solutions

- ✓ Maximized energy savings
- ✓ Compatible with full range of lighting control systems
- ✓ Easy to maintain on-site
- ✓ Easy to upgrade – to benefit from latest LED technology
- ✓ Best lighting quality and uniformity
- ✓ Designed for roadway lighting applications and standards

The RoadView incorporates several features that make it a versatile luminaire.

- ✓ Easy to install
- ✓ Easy to maintain
- ✓ Rotatable photocontrol receptacle
- ✓ Accommodates different types of control systems
- ✓ Accommodates 1.25" to 2" arm mounts
- ✓ Adjustable leveling features
- ✓ Surge protection
- ✓ Bird Guard
- ✓ Dimmable Drivers





Product features

Designed to accommodate the latest in street lighting control technology

Versatile and expandable LED boards

Highly efficient IP66 optics improve illuminance uniformity

Expanded flexibility in choosing the right wattage for the application



Easy to install and maintain

Tool-free access to electrical compartment




✓ Reversible mounting that accommodates different arm diameters

✓ Innovative thermal management provides longer LED lifetime

✓ 360° rotating twist-lock photocell receptacle

✓ Competitive high value performance luminaire




✓ Up to 100,000 hr rated life

✓ 3G tested per ANSI C136.31


✓ Modular design

✓ Protective lens


Dimensions



Fixture	Standard wattage	Weight		Length		EPA	
		lb.	kg.	in.	mm.	sq. ft.	sq. m.
RVS	55W32LED	23	10.4	21.38	543	0.53	0.049
	80W48LED	23	10.4	21.38	543	0.53	0.049
	110W64LED	26	11.8	25.25	641	0.60	0.056
	135W80LED	26	11.8	25.25	641	0.60	0.056
RVM	160W96LED	34	15.4	31.25	794	0.71	0.066
	190W112LED	34	15.4	31.25	794	0.71	0.066
	215W128LED	34	15.4	31.25	794	0.71	0.066
	245W144LED	37	16.8	35.25	895	0.78	0.072
	270W160LED	37	16.8	35.25	895	0.78	0.072



Energy



Fixture	Number of LEDs	Lamps	Typical wattage		Max. system current (amps)	LED drive current (mA)
			Lamp	System		
RVS	32	35W32LED4K	35	37	0.31	350
	32	55W32LED4K	55	56	0.47	530
	32	72W32LED4K	72	73	0.61	700
	48	55W48LED4K	55	53	0.44	350
	48	80W48LED4K	80	81	0.68	530
	48	108W48LED4K	108	105	0.88	700
	64	70W64LED4K	70	68	0.57	350
	64	110W64LED4K	110	104	0.87	530
	80	90W80LED4K	90	85	0.71	350
	80	135W80LED4K	135	129	1.08	530
RVM	96	110W96LED4K	110	105	0.88	350
	96	160W96LED4K	160	160	1.33	530
	96	215W96LED4K	215	208	1.73	700
	112	125W112LED4K	125	120	1.00	350
	112	190W112LED4K	190	183	1.53	530
	128	145W128LED4K	145	137	1.14	350
	128	215W128LED4K	215	209	1.74	530
	144	160W144LED4K	160	154	1.28	350
	144	245W144LED4K	245	235	1.96	530
	160	180W160LED4K	180	170	1.42	350
160	270W160LED4K	270	260	2.17	530	

CRI 70 minimum, Nominal ANSI CCT 4000K.




Maintenance



RoadView incorporates a removable power door



Quick disconnects provided




Power door easily removable for maintenance or upgrade

Luminaire options

- BL:** Bubble level
- RC:** Receptacle for photocell or shorting cap
- SR:** Strain relief (consult factory)
- HS:** Internal house side shield
- PH8:** Photocell and receptacle
- PH8/347:** Twist lock photoelectric cell
- PH8/480:** Twist lock photoelectric cell
- PHXL:** Extended life photoelectric cell

Driver options

- CDMG:** Programmable step-dimming
- DMG:** Dimming driver




- | | |
|---|--|
| 1. Surge protective device | 4. Strain relief |
| 2. Terminal block #2 - #14 AWG | 5. Reversible 4 bolt connection mounting |
| 3. Receptacle for photocell or shorting cap | 6. Bubble level |

RoadView

 Roadway

 Technical specs



Ordering guide

Example: RVM-215W96LED4K-G2-LE3-UNV-DMG-GY3

Series	LED module		Gen.	Optics	Voltage	Driver options	Luminaire options	Accessories	Finish
			G2						
RVM	3000K	4000K	G2 Gen2	LE2 Type II (ASYM) LE3 Type III (ASYM) LE4 Type IV (ASYM) LE5 ² Type V (ASYM)	HVU 347-480V UNV 120-277V	AST Pre-set driver for progressive start-up CDMGE25 8 hrs. 25% reduction CDMGE50 8 hrs. 50% reduction CDMGE75 8 hrs. 75% reduction CDMGM25 6 hrs. 25% reduction CDMGM50 6 hrs. 50% reduction CDMGM75 6 hrs. 75% reduction CDMGS25 4 hrs. 25% reduction CDMGS50 4 hrs. 50% reduction CDMGS75 4 hrs. 75% reduction CLO Pre-set driver to manage lumen depreciation DMG 0-10V OTL Pre-set driver to signal end of life of the lamp	APIFactory Installed NEMA label, ANSI C136.15 compliant BL Bubble Level HS House Side Shield, shield, 1 per 16 LED light engine RC Receptacle for twist-lock photocell or shorting cap, 3-pin SP2 20kV / 20kA Surge Protector (optional)	PH8 Twist-lock Photoelectric Cell, UNV (120-277VAC) PH8/347 Twist-lock Photoelectric Cell, (347VAC) PH8/480 Twist-lock Photoelectric Cell, (480VAC) PHXL Twist-lock Photoelectric Cell, extended life, UNV (120-277VAC) PH9 Shorting cap	BK Black BR Bronze GY3 Medium Grey WH White
	110W96LED3K	110W96LED4K							
	125W112LED3K	125W112LED4K							
	145W128LED3K	145W128LED4K							
	160W144LED3K	160W144LED4K							
	160W96LED3K	160W96LED4K							
	180W160LED3K	180W160LED4K							
	190W112LED3K	190W112LED4K							
	215W96LED3K	215W96LED4K							
	215W128LED3K	215W128LED4K							
	245W144LED3K	245W144LED4K							
	270W160LED3K	270W160LED4K							
RVS	3000K	4000K							
	35W32LED3K	35W32LED4K							
	55W32LED3K	55W32LED4K							
	55W48LED3K	55W48LED4K							
	70W64LED3K	70W64LED4K							
	72W32LED3K	72W32LED4K							
	80W48LED3K	80W48LED4K							
	90W80LED3K	90W80LED4K							
	108W48LED3K	108W48LED4K							
	110W64LED3K	110W64LED4K							
	135W80LED3K	135W80LED4K							

Find out more

See how **Lumec RoadView LED** roadway luminaires can help you succeed in your roadway lighting design goals. Contact your local Sales Representative or visit signify.com/prolighting for more information or to schedule a personalized demonstration.

Prior to ordering, consult specification sheets for the most current information, notes, and exclusions.

