



Project:	
Location:	
Cat.No:	
Type:	
Lamps:	Qty:
Notes:	

### Ordering Guide

Example: IT216 G H LED7 NF W

Product Code	IT216	LED Composite Inground
Rock Guard	G	Rock Guard *1
Finish	H N	Bronze Natural Brass
Source/Lumens	LED7	7W LED
Optics	NF FL	Narrow Flood Flood
CCT	W	Warm

\*1 Rock guard is optional and available in bronze and natural cast bronze only.  
\*2 Fixture will be shipped with lamp. Lamp not sold separately.

### Specifications

#### HOUSING:

Single-piece compression molded fiberglass reinforced polyester composite, factory pressure tested to ensure water will not wick or leak through. Trim ring is a compression molded polyester. Trim ring is a die-cast stainless steel. Trim ring is natural cast bronze. Rock guard used for directional glare control made of compression molded polyester.

#### FINISH:

Composite is textured, pressure formed, molded-in-color.

#### OPTICAL ASSEMBLY:

Lamps have 15° articulation either side of vertical and 358° rotation without interruption of beam pattern. Clear convex, tempered soda-lime glass for high impact resistance. 2,200-pound live-load rated, standard walk-over lens.

#### LAMPING:

7W lamp with 25° or 35° beam spread, 25,000 hours life. Color temperature (CCT): Warm White (3,000K nominal). No Mercury. Dimmable. Approximately 460 lumens.

#### ELECTRICAL ASSEMBLY:

Bi-pin socket type (GU5.3) with 250° C high temperature teflon coated wire leads. Double screw terminal socket. Step-down transformer reduces line voltage to 12 volts.

#### WARRANTY:

Five-year limited warranty.

#### CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards. ADA Compliant when flush mounted with CP2 or CPS2.

<b>Height :</b>	<b>Width:</b>	<b>Max. Weight:</b>
8 13/16" (224mm)	6 5/8" (169mm)	3.45 lb.

