





Project:	roject:		
Location:			
Cat.No:			
Туре:			
Lamps:	Qty:		
Notes:			

Stonco LytePro LED medium floodlight allows precision and flexibility in a compact design. The LPF3 features state-of-the-art long-life LED technology and is ideal for landscapes, accenting signage or displays, facades, and many other lighting applications.

Example: LPF3-C-4K-FL-S-F1-PCB-1-BZ

Ordering guide¹

Drive Color Series / # of COB² Distribution Mounting Options Finish Voltage Current Temperature LPF3 C LPF3 LytePro C 700 mA 4K 4000K3 FL Flood Slipfitter 2-3/8" O.D. F14 Single Fusing 120V **Textured Dark Bronze** F25 LED 5K 5000K3 SP Spot Trunnion **Double Fusing** 208V WН Textured White Medium F36 Double Fusing, Canada 240V Textured Dark Gray PCB7 277V Floodlight Photocontrol 85W DM258,9 Dynadimmer 347V 120-277V

Accessories - Ordering Guide (must be ordered separately)

Catalog #	Description
LPF3WG ^{10,11}	Wire Guard
LPF3SG ^{10,11}	Stone Guard

Footnotes:

- MTO configurations are assembled in the USA
- COB denotes Chip On Board LED platform.
- Both 4K and 5K options have a minimum 80 CRI. 'F1' for 120, 277, 347V.
- 'F2' for 208, 240V.
- 'F3' for 208, 240V Canadian double pull
- Specify voltage. 'PCB' not available with '8' universal voltage option.
- 'DM25' only available 120-277V and dims to 25% for 6 hours.
- Dynadimmer is suitable for use from -30°C to 40° temperature ambient only.

Stocked Luminaires – Ordering Guide^{12,13,14,15}

Catalog #	Description	Master Pack, QTY	UPC Code
STKLPF3S-8	LPF3, Slipfitter Mount, 120-277V	Yes, 2	786034956949

- Limited quantities stocked in our Carrollton RDC.
- Contact factory for availability of large order quantities
- All stock products are 'BZ' Textured Dark Bronze, '4K' Neutral White and 'FL' Flood Optics. Stock LPF products ship out of our Carrollton Distribution facility within 2-days of receipt of order.
- Always consult factory for current inventory levels. Larger quantities may be converted to MTO if necessary.
- LPF3 is provided with full 4-color POP packaging.





LytePro LED medium floodlight

Features

- · LPF3 flood distribution delivers 7,012 lumens at 85W, with an efficacy of 82 lumens per watt
- · LPF3 spot distribution delivers 6,807 lumens at 85W, with an efficacy of 80 lumens per watt
- · Effectively replaces equivalent 175-250W HID
- 4000K neutral white is standard, 5000K cool white is optional, minimum 80 CRI
- \cdot DLC certified optics provide excellent uniformity ideal for general facade, target and landscape illumination
- \cdot Fixtures are IP66 rated and suitable for use in ambients from -40°C to 40°C
- Rated system life of 80K hours for the driver and LED ($^{>}L_{_{70}}$) at ambients up to 30°C
- 5-year limited warranty, see philips.com/warranties for details
- LPF3 stocked in dark bronze, slipfitter mount, flood optic, 120-277V, and 4000K Neutral White for quick 2-day shipment
- · Additional made to order versions available that are assembled in the USA, consult factory for current lead time

Performance Specifications


Beam Specs	Flood (FL)	Spot (SP)
Initial Lumens (4K and 5K) ¹⁶	7,012	6,807
Average Wattage ¹⁷	85W	85W
Lumens/Watt	8q2	80
NEMA Beam	6H x 6V	3H x 3V
50% beam (horizontal X vertical)	101° x 97°	17° x 17°
10% beam (horizontal X vertical)	130° x 125°	41° x 38°
Max Candela	3,100 cd	33,122 cd


- Lumen values based on photometric tests performed in compliance with IESNA LM-79. System input wattage may vary based on input voltage, by up to +/- 8%, and based on manufacturer forward voltage, by up to +/- 4%.


Dimensions

Approximate luminaire weight -19lbs (8.6kg)

Fixture EPA -0.74 sq. ft.








Photometrics

Flood (FL)



Notes: Grid is in multiples of mounting height and values shown are in footcandles. Values shown are based on initial lumens.

LPF3 85W - 15' Mounting Height, 30° Tilt

0.20 0.44

20

15 12 10


1.0

1.7

Mounting Height 25

Multiplier


Spot (SP)



LPF3 85W - 20' Mounting Height, 0° Tilt Mounting Height 30 25 20 15 10 Multiplier 0.44 0.64 1.0 1.8

Accessory Details (must be ordered separately)

LPF3WG wire guard (field installed)



LPF3SG stone guard (field installed)



LytePro LED medium floodlight

Specifications

General Description

The Stonco LytePro LED Medium Floodlight 85W LPF3 combines excellent performance, design and value to meet the needs for the energy and budget conscious. The LPF3 is available with slipfitter or trunnion mounting and flood or spot optical distributions suitable for use on a wide range of applications. A single primary SKU is available in stock for 2-day quick ship while a more comprehensive offering is available made-to-order with multiple offerings that include fusing, photocontrol, Dynadimmer, NW and CW color temps and three standard finishes.

Housing

Die-cast housing houses both the LED and driver assemblies. Design incorporates integrated heatsinking to maximize thermal performance and reliability.

Mounting

The LPF3 is available with slipfitter or trunnion mounting to allow for wide range of aiming and adjustability. Caution: Stonco is not responsible for failure of mounting components supplied by others. Proper care should be exercised in mounting component selection and installation to insure adequate luminaire support, given system weight, vibration potential, exposure to the elements, thermal conditions present in the given application, etc. If luminaires are not properly supported and installed correctly per local codes and requirements, this may result in damage or injury caused by the luminaire, for which Stonco is not responsible.

IP Rating

Entire fixture is rated IP66, including driver and optical assemblies

LED Board and Array

The LPF3 utilizes three Citizen CLL032 COB (Chip On Board) LEDs. Provides up to 82 lm/W at the system level. Standard color temp is 4000K +/- 250K, with optional 5000K available. Both color temps have a minimum 80 CRI.

LED Thermal Management

Housing design integrates thermal heatsinking between the optical and driver assemblies, allowing for pass-through convective cooling which promotes airflow for improved and maximum heat dissipation. This results in maximized performance and reliability of critical components to ensure long LED system life

Optical Systems

LPF3 Flood 'FL' is standard with a Flood 'FL' optic that consists of a specular vacuum metalized reflector that provides a very uniform and highly efficient all purpose flood distribution. Optional Spot 'SP' optic consists of a TIR lens to provide a tight spot. Both optics are suitable for use in wide range of applications.

Energy saving benefits and controls

The LPF3 has a system efficacy of 82 lm/W at a system wattage of 85W using the flood distribution. With the spot distribution it has a system efficacy of 80 lm/W at a system wattage of 85W. It provides significant energy savings over traditional HID systems less controls. Optional Dynadimmer controls provides additional maximum energy savings by dimming to 25% low for 6 hours.

Electrical

Driver efficiency (>90% standard). 120-347V available (restrictions apply). Temp range: -40°C (-40°F) to 40°C (104°F). Open/short circuit protection. RoHS compliant. Surge protector standard and is in accordance with IEEE / ANSI C62.41.2 guidelines, with a surge current rating of 10,000 amps (10KVA).

Listings

Product is UL and cUL listed to the UL1598 standard, suitable for Wet Locations. Suitable for use in ambients from -40°C to 40°C (-40°F to 104°F). The LPF3 luminaire with either 4K Neutral White or 5K Cool White LEDs and flood or spot optics is DesignLights Consortium® qualified. Stock SKUs of the LPF family are made in China while all made-to-order configurations are assembled in the USA.

Finish

Each luminaire receives a fade and abrasion resistant, electrostatically applied, thermally cured, triglycidal isocyanurate (TGIC) textured polyester powdercoat finish. Standard finish on all stocked LPF luminaires is Textured Dark Bronze. Textured White and

Dark Gray are also available as optional colors for made-to-order products.

Warranty

LPF3 luminaires, the LED arrays, and the drivers are all covered by a 5-year limited warranty See philips.com/warranties for details.

Predicted Lumen Depreciation Data¹⁸

Ambient Temp. °C	TM-21 Calculated L ₇₀ hrs ^{18,19}	Reported L ₇₀ Per TM-21 ^{19,20}	Lumen Maint. % @60,000 hrs
up to 40°C	269,000 hrs	>48,000 hrs	91.5%

- Calculated performance derived from LED manufacturer's data and engineering design estimates, based on IESNA LM-80 methodology. Actual experience may vary due to field application conditions. L_{20} is the predicted time when LED performance depreciates to 70% of initial lumen output.
- Reported per IESNA TM21-11. Published L_{70} hours limited to 6 times actual LED test hours

